

# IP20 Cabinet Mount Drives

**7 Frame Sizes**  
**↑ 350HP**



## Powerful Performance

The Optidrive P2 offers the perfect combination of high performance together with ease of use to allow even the most demanding applications to be tackled easily.

**Optistick Smart**  
Rapid commissioning tool



Voltage	Frame	HP	Amps	MODEL CODE										List Price
				Product Family	Generation	Frame Size	Voltage Code	Output Current	Supply Phases	Power Type	EMC Filter	Brake Type	Enclosure	
200 - 240 Volt +/-10% 1 Phase Input	2	1	4.3	ODP - 2 - 2 2 010 - 1 H	F	4	2	-	S	N			\$1,310.00	
	2	2	7	ODP - 2 - 2 2 020 - 1 H	F	4	2	-	S	N			\$1,350.00	
	2	3	10.5	ODP - 2 - 2 2 030 - 1 H	F	4	2	-	S	N			\$1,480.00	
200 - 240 Volt +/-10% 3 Phase Input	2	1	4.3	ODP - 2 - 2 2 010 - 3 H	F	4	2	-	S	N			\$1,470.00	
	2	2	7	ODP - 2 - 2 2 020 - 3 H	F	4	2	-	S	N			\$1,510.00	
	2	3	10.5	ODP - 2 - 2 2 030 - 3 H	F	4	2	-	S	N			\$1,840.00	
	3	5	15	ODP - 2 - 3 2 050 - 3 H	F	4	2	-	S	N			\$2,900.00	
	3	7.5	24	ODP - 2 - 3 2 075 - 3 H	F	4	2	-	S	N			\$3,170.00	
	4	7.5	24	ODP - 2 - 4 2 075 - 3 H	F	4	2	-	T	N			\$3,950.00	
	4	10	30	ODP - 2 - 4 2 100 - 3 H	F	4	2	-	T	N			\$4,010.00	
	4	15	46	ODP - 2 - 4 2 150 - 3 H	F	4	2	-	T	N			\$4,340.00	
	5	20	60	ODP - 2 - 5 2 020 - 3 H	F	4	2	-	T	N			\$5,990.00	
	5	25	72	ODP - 2 - 5 2 025 - 3 H	F	4	2	-	T	N			\$6,500.00	
	6A	30	90	ODP - 2 - 6 2 030 - 3 H	F	4	2	-	M	N			\$9,240.00	
	6A	40	110	ODP - 2 - 6 2 040 - 3 H	F	4	2	-	M	N			\$11,090.00	
6B	50	150	ODP - 2 - 6 2 050 - 3 H	F	4	2	-	M	N			\$13,550.00		
6B	60	180	ODP - 2 - 6 2 060 - 3 H	F	4	2	-	M	N			\$15,390.00		
380 - 480 Volt +/-10% 3 Phase Input	2	1	2.2	ODP - 2 - 2 4 010 - 3 H	F	4	2	-	S	N			\$1,360.00	
	2	2	4.1	ODP - 2 - 2 4 020 - 3 H	F	4	2	-	S	N			\$1,470.00	
	2	3	5.8	ODP - 2 - 2 4 030 - 3 H	F	4	2	-	S	N			\$1,510.00	
	2	5	9.5	ODP - 2 - 2 4 050 - 3 H	F	4	2	-	S	N			\$1,840.00	
	3	7.5	14	ODP - 2 - 3 4 075 - 3 H	F	4	2	-	S	N			\$2,580.00	
	3	10	18	ODP - 2 - 3 4 100 - 3 H	F	4	2	-	S	N			\$2,895.00	
	3	15	24	ODP - 2 - 3 4 150 - 3 H	F	4	2	-	S	N			\$3,155.00	
	4	15	24	ODP - 2 - 4 4 150 - 3 H	F	4	2	-	T	N			\$3,965.00	
	4	20	30	ODP - 2 - 4 4 200 - 3 H	F	4	2	-	T	N			\$4,030.00	
	4	25	39	ODP - 2 - 4 4 250 - 3 H	F	4	2	-	T	N			\$4,355.00	
	4	30	46	ODP - 2 - 4 4 300 - 3 H	F	4	2	-	T	N			\$4,685.00	
	5	40	61	ODP - 2 - 5 4 040 - 3 H	F	4	2	-	T	N			\$6,030.00	
	5	50	72	ODP - 2 - 5 4 050 - 3 H	F	4	2	-	T	N			\$6,550.00	
	6A	60	90	ODP - 2 - 6 4 060 - 3 H	F	4	2	-	M	N			\$9,240.00	
	6A	75	110	ODP - 2 - 6 4 075 - 3 H	F	4	2	-	M	N			\$11,090.00	
	6B	100	150	ODP - 2 - 6 4 100 - 3 H	F	4	2	-	M	N			\$13,550.00	
	6B	150	180	ODP - 2 - 6 4 150 - 3 H	F	4	2	-	M	N			\$15,390.00	
	8	300	370	ODP - 2 - 8 4 300 - 3 H	F	4	2	-	T	N			\$41,000.00	
8	400	450	ODP - 2 - 8 4 400 - 3 H	F	4	2	-	T	N			\$42,000.00		
500 - 600 Volt +/-10% 3 Phase Input	2	1	2.1	ODP - 2 - 2 6 010 - 3 H	O	4	2	-	S	N			\$1,490.00	
	2	2	3.1	ODP - 2 - 2 6 020 - 3 H	O	4	2	-	S	N			\$1,605.00	
	2	3	4.1	ODP - 2 - 2 6 030 - 3 H	O	4	2	-	S	N			\$1,655.00	
	2	5	6.5	ODP - 2 - 2 6 050 - 3 H	O	4	2	-	S	N			\$2,005.00	
	2	7.5	9	ODP - 2 - 2 6 075 - 3 H	O	4	2	-	S	N			\$2,110.00	
	3	10	12	ODP - 2 - 3 6 100 - 3 H	O	4	2	-	S	N			\$3,175.00	
	3	15	17	ODP - 2 - 3 6 150 - 3 H	O	4	2	-	S	N			\$3,475.00	
	3	20	22	ODP - 2 - 3 6 200 - 3 H	O	4	2	-	S	N			\$3,715.00	
	4	20	22	ODP - 2 - 4 6 200 - 3 H	O	4	2	-	T	N			\$5,340.00	
	4	25	28	ODP - 2 - 4 6 250 - 3 H	O	4	2	-	T	N			\$5,885.00	
	4	30	34	ODP - 2 - 4 6 300 - 3 H	O	4	2	-	T	N			\$6,375.00	
	4	40	41	ODP - 2 - 4 6 400 - 3 H	O	4	2	-	T	N			\$6,955.00	
	5	50	54	ODP - 2 - 5 6 050 - 3 H	O	4	2	-	T	N			\$8,045.00	
	5	60	65	ODP - 2 - 5 6 060 - 3 H	O	4	2	-	T	N			\$9,365.00	
	6A	75	78	ODP - 2 - 6 6 075 - 3 H	O	4	2	-	M	N			\$13,650.00	
	6A	100	105	ODP - 2 - 6 6 100 - 3 H	O	4	2	-	M	N			\$16,400.00	
	6B	125	130	ODP - 2 - 6 6 125 - 3 H	O	4	2	-	M	N			\$17,700.00	
	6B	150	150	ODP - 2 - 6 6 150 - 3 H	O	4	2	-	M	N			\$19,250.00	

### Enclosure & Display Types



- F** Internal EMC Filter
- O** No Internal EMC Filter
- 1** No Internal Brake

NOT TO SCALE



### IP20

Size	2	3	4	5	6A	6B	8
in Height	8.7	10.3	16.5	19.1	24.2	28.6	39.2
in Width	4.3	5.2	6.3	8.7	15.2	13.0	19.0
in Depth	7.3	8.1	9.4	10.2	12.6	12.6	18.9
lb Weight	3.97	7.7	17.9	37.5	70.5	94.8	282.2

**Contact us** to discuss availability & pricing