

C-9506

Air Switching Cumulator

Description

The C-9506 Air Switching Cumulator switches output pressure from zero to full supply pressure when the pilot pressure reaches the switch point.

Refer to *C-9506 Air Switching Cumulator Product Bulletin (LIT-7171455)* for important product information.

Technical Specifications

C-9506 Air Switching Cumulator	
Action	Two Position DA
Switch Point	Adjustable from 2 to 12 psig (14 to 84 kPa) Factory Set at 9 psig (63 kPa)
Differential	1 psig (7 kPa)
Maximum Supply Pressure	25 psig (175 kPa)

Features

- ideally suited for exhaust damper applications requiring high output volume for quick operation
- adjustable switch point
- mounts in any position with integral mounting holes in base

Selection Charts

C-9506 Air Switching Cumulator

Code Number	Description
C-9506-1	Two-Position Cumulator

Accessories for C-9506

Code Number	Description
T-3100-6005	Air Connection Filter, 50/Pkg

Repair Information

If the C-9506 Air-Switching Cumulator fails to operate within its specifications, replace the unit. For a replacement cumulator, contact the nearest Johnson Controls® representative.



C-9506-1