



 PRODUCT-DETAILS

JSHD4 AK

JSHD4 AK Bottom part



360°

General Information

| | |
|-------------------------------|---|
| Extended Product Type: | JSHD4 AK |
| Product ID: | 2TLA020005R1900 |
| EAN: | 7350024483123 |
| Catalog Description: | JSHD4 AK Bottom part |
| Long Description: | <p>JSHD4 AK is a JSHD4 bottom part with a Cannon connector intended for replacement of former non modular Jokab JSHD4. It is used with any JSHD4 top part, except JSHD4-1, to form a complete three-position device. It is not compatible with the anti-tamper PCB.</p> <p>Three-position devices are used to allow a limited movement of the machine when the operator is in the dangerous area, for example during troubleshooting, test running and programming.</p> |
| Display Name: | JSHD4 AK |

Ordering

| | |
|--------------------------------|-----------------|
| Minimum Order Quantity: | 1 piece |
| Customs Tariff Number: | 85369095 |
| Product Main Type: | JSHD4 accessory |
| Product Name: | Bottom part |

Popular Downloads

| | |
|------------------------------------|-----------------|
| Data Sheet, Technical Information: | 2TLC010001C0202 |
| CAD Dimensional Drawing: | 2CDC001079B0201 |

Installation

| | |
|---------------------------|-----------------|
| Instructions and Manuals: | 2TLC172072M0201 |
| Wiring Diagram: | 2TLC010143D0201 |

Dimensions

| | |
|-----------------------------|----------|
| Product Net Depth / Length: | 50 mm |
| Product Net Height: | 50 mm |
| Product Net Width: | 33 mm |
| Product Net Weight: | 0.091 kg |

Technical

| | |
|---------------------------|---|
| Connection Configuration: | Cannon 12 male pins |
| Suitable For: | JSHD4-2 JSHD4-2 black JSHD4-3 JSHD4-4 JSHD4-5 |

Environmental

| | |
|-----------------------|------|
| Degree of Protection: | IP65 |
|-----------------------|------|

Material Compliance

| | |
|--|--|
| Conflict Minerals Reporting Template (CMRT): | 9AKK108467A5658 |
| REACH Declaration: | 2CMT2022-006480 |
| RoHS Declaration: | 2CMT2022-006499 |
| RoHS Information: | Following EU Directive 2011/65/EU and Amendment 2015/863 July 22, 2019 |
| Toxic Substances Control Act - TSCA: | 2CMT2023-006522 |
| WEEE Category: | Product Not in WEEE Scope |

Certificates and Declarations

| | |
|--|-------------------------|
| CQC Certificate: | No certification needed |
| cULus Certificate: | 2TLC010062D0201 |
| Declaration of Conformity - CCC: | No declaration needed |
| Declaration of Conformity - CE: | 2TLC172022D0201 |
| Declaration of Conformity - UKCA: | 2TLC010152D0201 |

Container Information

| | |
|--|---------------|
| Package Level 1 Units: | box 1 piece |
| Package Level 1 Width: | 145 mm |
| Package Level 1 Depth / Length: | 190 mm |
| Package Level 1 Height: | 35 mm |
| Package Level 1 Gross Weight: | 0.093 kg |
| Package Level 1 EAN: | 7350024483123 |

External Classifications and Standards

| | |
|--|---|
| eClass: | V11.0 : 27371392 |
| ETIM 7: | EC002886 - Accessories for agreement switch |
| ETIM 8: | EC002886 - Accessories/spare parts for agreement switch |
| ETIM 9: | EC002886 - Accessories/spare parts for agreement switch |
| IDEA Granular Category Code (IGCC): | 5219 >> Switch part or accessory |
| UNSPSC: | 39122221 |
| Object Classification Code: | X |

Categories

Products > Low Voltage Products and Systems > Control Products > Safety Products > Safety Control Devices

Products > Low Voltage Products and Systems > Control Products > Safety Products > Safety Control Devices > JSHD



