



Representative Image

**Catalog No. 2TLA050011R1432**

**Description: MKEY8, SOL NPT, 24V MET. FLEX KEY**

**UPC No 804325833431**

**Home > Machine Safety > Safety Sensors, Switches, Locks & Gate Boxes**

Mechanical Solenoid Safety interlock switch, die cast housing and head, spring lock (power to unlock), 2000N holding force. 24VDC coil, 2NC+ 1NO(locked)+2NC+ 1NO (actuator inserted). 3x 1/2NPT conduit entries. Delivered with metal flex key.

**Descriptors**

Category	Safety Sensors, Switches, Locks & Gate Boxes
Type	Safety Lock

**Specifications**

Product Class	Safety Locks & Process Locks
Product Main Type	MKey
Supply Voltage	24VDC
Outputs	Contact
Number of Outputs	4NC + 2NO
Degree of Protection	IP67

**Classifications**

ETIM 4	EC002593 - Position switch with interlocking
ETIM 5.0	EC002593 - Position switch with interlocking
ETIM 6.0	EC002593 - Position switch with interlocking
ETIM 7	EC002593 - Position switch with guard locking
ETIM 8 (Etim8)	EC002593 - Position switch with guard locking

**Dimensions**

Product Net Depth / Length	47 mm
Product Net Height	176 mm
Product Net Width	46 mm
Product Net Weight	0.78kg

**Safety Information**

Performance Level	Up to e
-------------------	---------