

- CE
- NEMA Size 6 & V 600
- IEC 600A



- Three Ratings
- One Small Size

CV Series
NEMA Size 6
IEC 600A

A

600Volt Nema Size 6 540A Starter 3 Pole Nema ICS-2 UL508 CSA 22.2

| Rating Nema Size 6 | Maximum Horsepower/KW Rating 3 Phase HP/KW | | | | Open Type | Discount Schedule JC11 |
|-----------------------|---|---------|---------|---------|---------------|---------------------------|
| 600V | 200/208V | 2500V | 460V | 575V | Catalog # | Price |
| HP/KW | 150/112 | 200/150 | 400/300 | 400/300 | CV13U030606-* | \$3898 |

1000Volt 400AMP Contactor 3 Pole IEC 947-4-1 UL508 CSA 22.2

| Rating 600A 1000V | Maximum Horsepower/KW Rating 3 Phase HP/KW | | | | | | Open Type | Discount Schedule JC11 |
|----------------------|--|----------|---------|---------|----------|----------|---------------|---------------------------|
| 1000V | 200/208V | 220/240V | 400V | 460V | 575/600V | 660-690V | Catalog # | Price |
| HP/KW | 200/150 | 200/150 | 250/187 | 400/300 | 600/450 | 650/485 | CV13U036A06-* | \$4081 |

1500 Volt 600 AMP Starter 3 Pole ICS 2-9 IEC 947-4-1 (1000V) UL508 (1500V) CSA 22.2 (1500V)

| Rating 600A Nema V600 | Maximum Horsepower/KW Rating 3 Phase HP/KW | | | | | | | | Open Type | Discount Schedule JC11 |
|--------------------------|--|----------|---------|---------|----------|----------|----------|-----------|---------------|---------------------------|
| 1500V | 200/208V | 220/240V | 400V | 460V | 575/600V | 660-690V | 1000V | 1500V | Catalog # | Price |
| HP/KW | 200/150 | 200/150 | 250/187 | 400/300 | 600/450 | 650-485 | 1000/750 | 1200/900 | CV13U036A15-* | \$4483 |
| Nema V600 | 200/150 | 200/150 | 375/280 | 500/350 | 600/470 | | 1100/820 | 1600/1200 | CV13U036V15-* | \$4483 |

Options (Discount Schedule JC11) Field Kits

| Description | Catalog # | Price |
|--------------------------------------|-----------|-------|
| Wire Size (2) #2-600 mcm | KVC6-2 | \$156 |
| Aux Contact Kit 2N/O 2N/C 10A 600VAC | AK1 | \$73 |
| Aux. Contact Kit 2N/O 2N/C 10MA 5VDC | AK3 | \$220 |

Replacement Parts (Discount Schedule JC80)

| Description | Catalog # | Price |
|--|---------------|-------|
| Interrupter Phase Assembly | A77460880A-2 | \$851 |
| Coil 110/120V 50/60 HZ | A77-460930A-1 | \$284 |
| Coil 220/240V 50/60 HZ | A77-460930A-2 | \$284 |
| Coil 380/415V 50/60 HZ | A77-460930A-3 | \$284 |
| Coil 440/480V 50/60 HZ | A77-460930A-4 | \$284 |
| Coil 125V DC | A77-460930A-7 | \$284 |
| Coil 250V DC | A77-460930A-8 | \$284 |
| Control PAK 110/120 50/60 HZ | A77-460916A-4 | \$258 |
| Control PAK 110/120 50/60 HZ | A77-460916A-5 | \$258 |
| Control PAK 380-415V 50/60 HZ 440-480V 50/60 HZ | A77-460916A-6 | \$258 |
| Aux. Contact Kit 2N/O 1N/C +1 N/C Late Break | AK Std. | \$ 92 |

Ordering Information

- Use complete catalog number when ordering. Replace the (*) with the suffix from the coil table.
- Order Heaters at \$18.00 each from page A35
- Engineering Data page A19.
- Renewal Parts page A17.

*** Coil Table**

| Voltage | Suffix |
|---------|--------|
| 120 AC | -76 |
| 240 AC | -26 |
| 380 AC | -38 |
| 460 AC | -46 |
| 125V DC | -125 |
| 250V DC | -250 |