

Posi-Lok™ Plugs and Panels



MALE PANEL PART NUMBERS		
RECEPTACLES PER PANEL	MALE PANELS	COVER COLOR CODE
3	E0400-1660	GR, WH, BK
4	E0400-1661-NN	GR, BK, RD, BU
4	E0400-1672	GR, WH, BK, RD
4	E0400-1862-NN	GR, BRN, ORG, YEL
5	E0400-1662	GR, WH, BK, RD, BU
5	E0400-1703	GR, WH, BRN, ORG, YEL
6	E0400-1860	GR, WH, WH, BK, RD, BU

E0400 SERIES

3, 4, 5 OR 6 WIRE SYSTEM, RATED UP TO 400 AMPS, CONTINUOUS, 600 VOLTS, 105° C.

- GR = Green
- WH = White
- BK = Black
- RD = Red
- BU = Blue
- BRN = Brown
- ORG = Orange
- YEL = Yellow
- NN = Panel without Neutral

Other Color Codes available; consult factory.

Add "LS" suffix to end of part number to order panels with a limit switch. Available on all positions. Consult factory.

Limit switch ratings are 15A-125, 250, 480VAC.

.5A 125VDC

.25A 250VDC

Plugs must be ordered separately. See chart.

