

Roughneck[®] Connectors

ROUGHNECK PLUGS E1049 SERIES

FOR 313-535 MCM CABLE, 1,000 VOLTS.

NOTE: MALE PLUGS AND RECEPTACLES SHOULD BE USED ON THE POWER SOURCE SIDE. FEMALE PLUG AND RECEPTACLES SHOULD BE USED ON THE LOAD DISTRIBUTION SIDE. DO NOT DISCONNECT UNDER LOAD.



*COMPLETE MALE AND COMPLETE FEMALE PLUGS INCLUDE DUST CAP.

MALE PLUG				
TYPE OF CONNECTION AND WIRE SIZE	COLOR	COMPLETE MALE CONNECTOR PART NO. *	INSULATOR ONLY PART NO.	CONTACT ONLY PART NO.
HEXAGON CRIMP OR SOLDER FOR 535 MCM	Black	E1049-1	A201106-1	A201107-1
	Yellow	E1049-2	A201106-2	
	Red	E1049-3	A201106-3	
	Orange	E1049-4	A201106-4	
	Green	E1049-5	A201106-5	
	White	E1049-6	A201106-6	
	Blue	E1049-7	A201106-7	
	Brown	E1049-8	A201106-8	

FEMALE PLUG				
TYPE OF CONNECTION AND WIRE SIZE	COLOR	COMPLETE FEMALE CONNECTOR PART NO. *	INSULATOR ONLY PART NO.	CONTACT ONLY PART NO.
HEXAGON CRIMP OR SOLDER FOR 535 MCM	Black	E1049-50	A201100-1	A201103-1
	Yellow	E1049-51	A201100-2	
	Red	E1049-52	A201100-3	
	Orange	E1049-53	A201100-4	
	Green	E1049-54	A201100-5	
	White	E1049-55	A201100-6	
	Blue	E1049-56	A201100-7	
	Brown	E1049-57	A201100-8	

