

# Roughneck® Connectors



MALE PLUG				
TYPE OF CONNECTION AND WIRE SIZE	COLOR	COMPLETE MALE CONNECTOR PART NO. *	INSULATOR ONLY PART NO.	CONTACT ONLY PART NO.
HEXAGON CRIMP OR SOLDER FOR 444 MCM	Black	E1049-201	A201106-1	A201107-8
	Yellow	E1049-202	A201106-2	
	Red	E1049-203	A201106-3	
	Orange	E1049-204	A201106-4	
	Green	E1049-205	A201106-5	
	White	E1049-206	A201106-6	
	Blue	E1049-207	A201106-7	
	Brown	E1049-208	A201106-8	

\*Complete male and complete female plugs include dust cap.

FEMALE PLUG				
TYPE OF CONNECTION AND WIRE SIZE	COLOR	COMPLETE FEMALE CONNECTOR PART NO. *	INSULATOR ONLY PART NO.	CONTACT ONLY PART NO.
HEXAGON CRIMP OR SOLDER FOR 444 MCM	Black	E1049-250	A201100-1	A201103-8
	Yellow	E1049-251	A201100-2	
	Red	E1049-252	A201100-3	
	Orange	E1049-253	A201100-4	
	Green	E1049-254	A201100-5	
	White	E1049-255	A201100-6	
	Blue	E1049-256	A201100-7	
	Brown	E1049-257	A201100-8	

\*Complete male and complete female plugs include dust cap.

## ROUGHNECK PLUGS E1049 SERIES

FOR 313- 444MCM CABLE, 1,000 VOLTS.

NOTE: MALE PLUGS AND RECEPTACLES SHOULD BE USED ON THE POWER SOURCE SIDE. FEMALE PLUG AND RECEPTACLES SHOULD BE USED ON THE LOAD DISTRIBUTION SIDE. DO NOT DISCONNECT UNDER LOAD.

