

Roughneck® Connectors

ROUGHNECK PLUGS E1049 SERIES

FOR 313-777 MCM CABLE, 1,000 VOLTS.

NOTE: MALE PLUGS AND RECEPTACLES SHOULD BE USED ON THE POWER SOURCE SIDE. FEMALE PLUG AND RECEPTACLES SHOULD BE USED ON THE LOAD DISTRIBUTION SIDE. DO NOT DISCONNECT UNDER LOAD.

*COMPLETE MALE AND COMPLETE FEMALE PLUGS INCLUDE DUST CAP.

MALE PLUG				
TYPE OF CONNECTION AND WIRE SIZE	COLOR	COMPLETE MALE CONNECTOR PART NO.*	INSULATOR ONLY PART NO.	CONTACT ONLY PART NO.
HEXAGON CRIMP OR SOLDER FOR 777 MCM	Black	E1049-21	A201106-1	A201107-3
	Yellow	E1049-22	A201106-2	
	Red	E1049-23	A201106-3	
	Orange	E1049-24	A201106-4	
	Green	E1049-25	A201106-5	
	White	E1049-26	A201106-6	
	Blue	E1049-27	A201106-7	
	Brown	E1049-28	A201106-8	

FEMALE PLUG				
TYPE OF CONNECTION AND WIRE SIZE	COLOR	COMPLETE FEMALE CONNECTOR PART NO. *	INSULATOR ONLY PART NO.	CONTACT ONLY PART NO.
HEXAGON CRIMP OR SOLDER FOR 777 MCM	Black	E1049-70	A201100-1	A201103-3
	Yellow	E1049-71	A201100-2	
	Red	E1049-72	A201100-3	
	Orange	E1049-73	A201100-4	
	Green	E1049-74	A201100-5	
	White	E1049-75	A201100-6	
	Blue	E1049-76	A201100-7	
	Brown	E1049-77	A201100-8	

