

# Roughneck<sup>®</sup> Connectors

## ROUGHNECK PLUGS E1049 SERIES

FOR 313-777 MCM CABLE, 1,000 VOLTS.

NOTE: MALE PLUGS AND RECEPTACLES SHOULD BE USED ON THE POWER SOURCE SIDE. FEMALE PLUG AND RECEPTACLES SHOULD BE USED ON THE LOAD DISTRIBUTION SIDE. DO NOT DISCONNECT UNDER LOAD.



MALE PLUG				
TYPE OF CONNECTION AND WIRE SIZE	COLOR	COMPLETE MALE CONNECTOR PART NO. *	INSULATOR ONLY PART NO.	CONTACT ONLY PART NO.
HEXAGON CRIMP OR SOLDER FOR 313 MCM	Black	E1049-31	A201106-1	A201107-4
	Yellow	E1049-32	A201106-2	
	Red	E1049-33	A201106-3	
	Orange	E1049-34	A201106-4	
	Green	E1049-35	A201106-5	
	White	E1049-36	A201106-6	
	Blue	E1049-37	A201106-7	
	Brown	E1049-38	A201106-8	

\*Complete male and complete female plugs include dust cap.

FEMALE PLUG				
TYPE OF CONNECTION AND WIRE SIZE	COLOR	COMPLETE FEMALE CONNECTOR PART NO. *	INSULATOR ONLY PART NO.	CONTACT ONLY PART NO.
HEXAGON CRIMP OR SOLDER FOR 313 MCM	Black	E1049-80	A201100-1	A201103-4
	Yellow	E1049-81	A201100-2	
	Red	E1049-82	A201100-3	
	Orange	E1049-83	A201100-4	
	Green	E1049-84	A201100-5	
	White	E1049-85	A201100-6	
	Blue	E1049-86	A201100-7	
	Brown	E1049-87	A201100-8	

\*Complete male and complete female plugs include dust cap.

