

Cam-Lok® Standard Series



E1018-1600

All Cam-Lok part numbers available in convenient, single-use, color-coded packaging.

INSULATED RECEPTACLES			
	COLOR	MALE COMPLETE PART NO.	FEMALE COMPLETE PART NO.
3/4" THREADED STUD	BLACK	E1018-1600	E1018-1631
	RED	E1018-1602	E1018-1633
	GREEN	E1018-1604	E1018-1635
	WHITE	E1018-1605	E1018-1636
	BLUE	E1018-1606	E1018-1637
	BROWN	E1018-1607	E1018-1638
	ORANGE	E1018-1603	E1018-1634
	YELLOW	E1018-1601	E1018-1632

Stud size 1/2"-13, maximum torque 40 ft. lbs.

E 1018 Series



E1018-1631

INSULATED RECEPTACLES			
	COLOR	MALE COMPLETE PART NO.	FEMALE COMPLETE PART NO.
1 1/8" THREADED STUD	BLACK	E1018-1600S	E1018-1631S
	RED	E1018-1602S	E1018-1633S
	GREEN	E1018-1604S	E1018-1635S
	WHITE	E1018-1605S	E1018-1636S
	BLUE	E1018-1606S	E1018-1637S
	BROWN	E1018-1607S	E1018-1638S
	ORANGE	E1018-1603S	E1018-1634S
	YELLOW	E1018-1601S	E1018-1632S

Stud size 1/2"-13, maximum torque 40 ft. lbs.

CAM-LOK STANDARD SERIES "BALL NOSE" DESIGN RECEPTACLES AND PLUGS HAVE BEEN USED FOR YEARS IN SHIPYARDS, CONSTRUCTION SITES AND POWER PLANTS. THEY HAVE BECOME THE STANDARD BY THE BROADCAST INDUSTRY IN CANADA, AS WELL AS THE WELDING INDUSTRY IN THE UNITED STATES.

RATINGS: 600 VOLTS UP TO 400 AMPERES CONTINUOUS

STANDARD MATERIALS
CABLE SIZE: #2 - 4/0
RECEPTACLE BODY: TPE
CONTACT: BRASS

AGENCY APPROVALS
CSA CERTIFIED LR13963

ENVIRONMENTAL RATING: NEMA 3R

