

Posi-Lok™ Plugs and Panels



FEMALE PANEL PART NUMBERS		
RECEPTACLES PER PANEL	FEMALE PANELS	COVER COLOR CODE
3	E0200-1685	GR, WH, BK
4	E0200-1686-NN	GR, BK, RD, BU
4	E0200-1696	GR, WH, BK, RD
4	E0200-1892-NN	GR, BRN, ORG, YEL
5	E0200-1687	GR, WH, BK, RD, BU
5	E0200-1890	GR, WH, BRN, ORG, YEL
6	E0200-1885	GR, WH, WH, BK, RD, BU

GR = Green WH = White BK = Black RD = Red BU = Blue
 BRN = Brown ORG = Orange YEL = Yellow NN = Panel without Neutral

Other Color Codes available; consult factory.

Add "LS" suffix to end of part number to order panels with a limit switch. Available on last position only. Example: E0200-1687LS.

Limit switch ratings are 5A, 250VAC.

Plugs must be ordered separately. See below.



Male Plug Assembled length is 8 3/4"

MALE PLUG				
DESCRIPTION	POSITION	MALE COMPLETE PART NO.	MALE CONTACT ONLY PART NO.	MALE INSULATOR POLARIZING SHELL PART NO.
Crimp #2-2/0	Green	E0200-141	A201293-5	A201315-3
	White	E0200-142	A201293-5	A201315-2
	Black	E0200-143	A201293-5	A201315-1
#2=190 AMPS #1=200 AMPS #1/0=200 AMPS #2/0=200 AMPS	Red	E0200-144	A201293-5	A201315-5
	Blue	E0200-145	A201293-5	A201315-4
	Brown	E0200-147	A201293-5	A201315-9
	Orange	E0200-148	A201293-5	A201315-10
	Yellow	E0200-149	A201293-5	A201315-8
Double Set Screw #2-2/0 #2=190 AMPS #1=200 AMPS #1/0=200 AMPS #2/0=200 AMPS	Green	E0200-181	A201293-1	A201315-3
	White	E0200-182	A201293-1	A201315-2
	Black	E0200-183	A201293-1	A201315-1
	Red	E0200-184	A201293-1	A201315-5
	Blue	E0200-185	A201293-1	A201315-4
	Brown	E0200-199	A201293-1	A201315-9
	Orange	E0200-195	A201293-1	A201315-10
	Yellow	E0200-192	A201293-1	A201315-8

E0200 SERIES

3, 4, 5 OR 6 WIRE SYSTEM, RATED UP TO 200 AMPS, CONTINUOUS, 600 VOLTS, 105° C.

NOTES: AMPACITY IS BASED ON CABLE SIZE OR CONTACT RATING, WHICHEVER IS LESS.

PANEL DOES NOT INCLUDE ENCLOSURE OR BREAKERS. POSI-LOK SYSTEM MUST BE INSTALLED PER LOCAL AND NATIONAL STANDARDS. PANEL RECEPTACLES HAVE LOCK WASHERS, FLAT WASHERS AND JAM NUTS INCLUDED.