

Wall Mount Inline Receptacle (MS3100 Type) - C3100 Class A



- Includes adapter designed to accept C3057 and MS3057 standard backshells.
- Available with optional RoHS compliant plating.

DIMENSIONS

PART NUMBER	A REF.	B REF.	C DIA. REF.	D REF.	E MAX./MIN.	F MAX.	G DIA. REF.	H THREAD	J THREAD
C3100A10SL-	1.00 (25.4)	0.72 (18.3)	0.45 (11.4)	0.56 (14.3)	0.16 (4.0) / 0.06 (1.6)	1.53 (38.9)	0.12 (3.1)	5/8-24UNEF	5/8-24UNEF
C3100A12S-	1.09 (27.8)	0.81 (20.6)	0.56 (14.2)	0.56 (14.3)	0.16 (4.0) / 0.06 (1.6)	1.69 (42.9)	0.12 (3.1)	3/4-20UNEF	5/8-24UNEF
C3100A12-	1.09 (27.8)	0.81 (20.6)	0.56 (14.2)	0.75 (19.1)	0.16 (4.0) / 0.06 (1.6)	2.06 (52.4)	0.12 (3.1)	3/4-20UNEF	5/8-24UNEF
C3100A14S-	1.19 (30.2)	0.91 (23)	0.68 (17.3)	0.56 (14.3)	0.16 (4.0) / 0.06 (1.6)	1.69 (42.9)	0.12 (3.1)	7/8-20UNEF	3/4-20UNEF
C3100A14-	1.19 (30.2)	0.91 (23)	0.68 (17.3)	0.75 (19.1)	0.16 (4.0) / 0.06 (1.6)	2.06 m(52.4)	0.12 (3.1)	7/8-20UNEF	3/4-20UNEF
C3100A16S-	1.28 (32.5)	0.97 (24.6)	0.81 (20.5)	0.56 (14.3)	0.16 (4.0) / 0.06 (1.6)	1.69 (42.9)	0.12 (3.1)	1-20UNEF	7/8-20UNEF
C3100A16-	1.28 (32.5)	0.97 (24.6)	0.81 (20.5)	0.75 (19.1)	0.16 (4.0) / 0.06 (1.6)	2.06 (52.4)	0.12 (3.1)	1-20UNEF	7/8-20UNEF
C3100A18-	1.38 (34.9)	1.06 (27)	0.93 (23.7)	0.75 (19.1)	0.20 (5.1) / 0.09 (2.4)	2.06 (52.4)	0.12 (3.1)	1 1/8-18UNEF	1-20UNEF
C3100A20-	1.50 (38.1)	1.16 (29.4)	1.06 (26.9)	0.75 (19.1)	0.20 (5.1) / 0.09 (2.4)	2.19 (55.6)	0.12 (3.1)	1 1/4-18UNEF	1 3/16-18UNEF
C3100A22-	1.63 (41.3)	1.25 (31.8)	1.18 (30.0)	0.75 (19.1)	0.20 (5.1) / 0.09 (2.4)	2.19 (55.6)	0.12 (3.1)	1 3/8-18UNEF	1 3/16-18UNEF
C3100A24-	1.75 (44.5)	1.38 (34.9)	1.31 (33.2)	0.81 (20.6)	0.20 (5.1) / 0.09 (2.4)	2.31 (58.7)	0.15 (3.7)	1 1/2-18UNEF	1 7/16-18UNEF
C3100A28-	2.00 (50.8)	1.56 (39.7)	1.53 (38.8)	0.81 (20.6)	0.20 (5.1) / 0.09 (2.4)	2.31 (58.7)	0.15 (3.7)	1 3/4-18UNEF	1 7/16-18UNEF
C3100A32-	2.25 (57.2)	1.75 (44.5)	1.78 (45.1)	0.88 (22.2)	0.36 (9.1) / 0.13 (3.2)	2.44 (61.9)	0.17 (4.4)	2-18UNS	1 3/4-18UNS
C3100A36-	2.50 (63.5)	1.94 (49.2)	2.00 (50.7)	0.88 (22.2)	0.36 (9.1) / 0.13 (3.2)	2.44 (61.9)	0.17 (4.4)	2 1/4-16UN	2-18UNS

Note: Dimensions in inches (mm).

