



Class I, Div. 1 & 2, Groups C,D
Class I, Zones 1 & 2, Groups IIB, IIA
Class II, Div. 1 & 2, Groups E,F,G
Class III
NEMA 7(C,D) 9(E,F,G)



Files 23689 or 25217

See files for details or call Killark.

FEATURES-SPECIFICATIONS

Applications

- Hazardous areas due to the presence of flammable gases or vapors, combustible dusts or easily ignitable fibers or flyings
- Installations at petroleum refineries, chemical and petrochemical plants, storage areas and other processing facilities where hazardous substances are handled or stored
- Use as motor circuit disconnect and provide short circuit protection of lighting and power circuits

Features

- Rectangular bolted cover design provide for attractive, compact, uniform installation
- Enclosure and external handle is cast copper-free aluminum alloy (less than 4/10 of 1%)
- Interior handle mechanism and hardware are dichromate over cadmium finish sheet steel for maximum strength and corrosive resistance
- Cover bolts are stainless steel
- Two drilled and tapped conduit openings one top and one bottom standard on all assemblies
- Custom drilled and tapped conduit openings available on any of the four sides. (See Conduit Opening Data Chart on page E37).
- External handle is vault type with standard provisions for locking in the "OFF" position with up to three padlocks
- Cutler-Hammer Visi-Flex Model A, Deion switches are used in all 30, 60 and 100 Ampere assemblies
- Cutler-Hammer Type DS switch is used in the 200 Ampere assembly

XFS DISCONNECT SWITCHES-FUSIBLE				
CATALOG NUMBER	SWITCH RATING AMP	FUSE KIT RATING		
		AMP	VOLT	TYPE
25XFS-30-30N3	30	30	250	NEC. K or H
25XFS-60-30N3	30	60	250	NEC. K or H
25XFS-100-30N3	30	100	250	NEC. K or H
60XFS-30-30J3	30	30	600	CLASS J
60XFS-30-30N3	30	30	600	NEC. K or H
60XFS-60-30J3	30	60	600	CLASS J
60XFS-60-30N3	30	60	600	NEC. K or H
25XFS-30-60N3	60	30	250	NEC. K or H
25XFS-60-60N3	60	60	250	NEC. K or H
25XFS-100-60N3	60	100	250	NEC. K or H
60XFS-30-60J3	60	30	600	CLASS J
60XFS-30-60N3	60	30	600	NEC. K or H
60XFS-60-60J3	60	60	600	CLASS J
60XFS-60-60N3	60	60	600	NEC. K or H
25XFS-60-100N3	100	60	250	NEC. K or H
25XFS-100-100N3	100	100	250	NEC. K or H
25XFS-200-100N3	100	200	250	NEC. K or H
60XFS-60-100J3	100	60	600	CLASS J
60XFS-60-100N3	100	60	600	NEC. K or H
60XFS-100-100J3	100	100	600	CLASS J
60XFS-100-100N3	100	100	600	NEC. K or H
60XFS200-100J3	100	200	600	CLASS J
60XFS200-100N3	100	200	600	NEC. K or H
25XFSW200-200N3	200	200	250	NEC. K or H
60XFSW200-200N3	200	200	600	NEC. K or H
25XFSW400-200N3	200	400	250	NEC. K or H
60XFSW400-200N3	200	400	600	NEC. K or H
60XFSW200-200J3	200	200	600	CLASS J

MODIFICATIONS	
SUFFIX NUMBER	DESCRIPTION
SU2	Hinge installed (standard on 200A)
SU3	Drain and breather installed
SU40	Lock "ON"
KIT-251	100 Amp ground lug
KIT-252	225 Amp ground lug

