



PULLING ELBOW & DUCT SEAL • STANDARD AND HOSTILE LOCATIONS



Duct seal

UL LISTED - File E E22699

SP Certified - File LR11852

See files for details or call Killark.

FEATURES-SPECIFICATIONS

Applications

- 90° pulling elbows are used to accommodate pulling conductors through a sharp bend in the conduit system

Features

- Designed for easier wire pulling
- Includes Cover and Gasket

Material/Finish

Copper-free Aluminum
(less than 4/10 of 1%)

- Electrostatically applied powder coating

PULLING ELBOWS FOR THREADED CONDUIT

| CATALOG NUMBER | HUB SIZE | TYPE |
|----------------|----------|------|
| CL-1 | 1/2" | CL |
| CL-2 | 3/4" | |
| CL-3 | 1" | |
| CLM-1 | 1/2" | CLM |
| CLM-2 | 3/4" | |
| CLM-3 | 1" | |

① Raintight/concrete tight

PULLING ELBOWS FOR THINWALL CONDUIT^②

| CATALOG NUMBER | HUB SIZE |
|----------------|----------|
| TWCL-1 | 1/2" |
| TWCL-2 | 3/4" |

② Set screw in each hub

Duct Seal is a soft, non-hardening weather-proof compound, easily applied in all working temperatures. It is non-staining, can be painted, is an excellent moisture barrier for weather-sealing service entries, electrical cables, conduit ducts, etc.

| DUCT SEAL | |
|----------------|-------|
| CATALOG NUMBER | SIZE |
| DS-1 | 1-lb. |
| DS-5 | 5-lb. |

DIMENSIONS

| SIZE | A | B | C | D | E |
|------|-------------|--------------|--------------|-------------|---------------|
| 1/2" | 1-1/4" (32) | 2-9/16" (65) | 1-3/8" (35) | 1-1/4" (32) | 1-7/16" (37) |
| 3/4" | 1-3/8" (35) | 2-3/4" (70) | 1-9/16" (40) | 1-3/8" (35) | 1-17/32" (39) |
| 1" | 1-3/4" (44) | 3-1/8" (79) | 1-3/4" (44) | 1-3/4" (44) | 1-23/32" (44) |

