



**TWOLRL Type**



**TWOT Type**



LISTED - FILE E3397



CERTIFIED - FILE LR11852

See files for details or call Killark.

**FEATURES-SPECIFICATIONS**

**Applications**

- For use with E.M.T conduit thin wall
- To make bends in the conduit system
- Connect conduit sections
- Provide access to the conduit system
- As a pulling outlet
- Provide openings for taps or splices

**Features**

- Easy installation (screwdriver is only tool required)
- Complete selection of sizes and hub configurations

**Material/Finish**

**Copper-free Aluminum**  
(less than 4/10 of 1%)

- Electrostatically applied powder coating
- Aluminum and steel/iron type 5 covers and gaskets can be used with TW series bodies. See page F23

TWO LRL TYPE CONDUIT BODY									
CATALOG NUMBER	CONDUIT SIZE	A	B	C	D	E	F	G	VOLUME CU. IN.
TWOLRL-1	1/2"	4-1/2" (114)	1-5/16" (33)	3-1/8" (79)	1-1/8" (29)	3-1/2" (89)	2-3/16" (56)	5/8" (16)	4.0
TWOLRL-2	3/4"	5-3/16" (132)	1-1/2" (38)	3-3/4" (95)	1-1/4" (32)	4-1/8" (105)	2-5/16" (59)	3/4" (19)	7.0
TWOLRL-3	1"	6-1/4" (159)	1-3/4" (44)	4-1/2" (114)	1-9/16" (40)	4-7/8" (124)	2-13/16" (71)	7/8" (22)	12.0

TWO T TYPE CONDUIT BODY									
CATALOG NUMBER	HUB SIZE	DIMENSIONS							VOLUME CU. IN.
		A	B	C	D	E	F	G	
TWOT-1	1/2"	5-3/16" (132)	15/16" (24)	2-1/4" (57)	1-1/8" (29)	3-1/2" (89)	—	5/8" (16)	4.0
TWOT-2	3/4"	5-3/4" (146)	1-1/2" (38)	2-5/16" (59)	1-3/16" (30)	4-1/8" (105)	—	3/4" (19)	7.0
TWOT-3	1"	7" (178)	1-3/4" (44)	3" (76)	1-9/16" (40)	4-7/8" (124)	—	15/16" (24)	12.0
TWOT-4	1-1/4"	8-11/16" (221)	2-1/2" (64)	3-1/2" (89)	2-3/16" (56)	6-1/2" (165)	—	1-3/16" (30)	32.0
TWOT-5	1-1/2"	8-1/8" (206)	2-1/2" (64)	3-3/8" (86)	2-3/16" (56)	6-1/2" (165)	—	1-3/8" (32)	36.0
TWOT-6	2"	10" (254)	3-1/8" (79)	3-3/4" (95)	2-3/4" (70)	8-5/8" (219)	—	1-5/8" (38)	70.0

**Dimensions**

