



METAL HALIDE PULSE, 150-200W MOGUL BASE HID



Pendant
w/ 5-1/2"
Globe & Guard



Flexible Pendant
w/ 5-1/2"
Refractor & Guard



Pendant
w/ 7-3/4"
Globe & Guard



Flexible Pendant
w/ 7-3/4"
Refractor & Guard



Pendant
w/ Enclosed Reflector

Class I, Div. 2, Groups A,B,C,D^①
Class I, Zone 2, Groups IIC, IIB, IIA
Class II, Div. 1 & 2, Groups E,F,G
Class III
Suitable for wet locations
NEMA 3, 4, 4X
IP66

- File E10514 (Hazardous & Marine)

Certified - File LR11713

NR Restricted Breathing Option^⑤

Class I, Zone 2 AEx nAnR

Class I, Zone 2 Ex nR

VM 150 - 200 WATT METAL HALIDE PULSE PENDANT										
DESCRIPTION				5-1/2" OPTIC THREAD SIZE ^②			7-3/4" OPTIC THREAD SIZE ^②			
WATTS	ANSI	HUB SIZE ^③	VOLTAGE ^④	GLOBE & GUARD	TYPE I GLASS REFRACTOR & GUARD	TYPE V GLASS REFRACTOR & GUARD	GLOBE & GUARD	TYPE I GLASS REFRACTOR & GUARD	TYPE V GLASS REFRACTOR & GUARD	ENCLOSED REFLECTOR
150	M102	3/4"	Quad Tri 480	VM3P150A2GLG	VM3P150A2R1G	VM3P150A2R5G	VM4P150A2GLG	VM4P150A2R1G	VM4P150A2R5G	VM4P156A2ERN
				VM3P156A2GLG	VM3P156A2R1G	VM3P156A2R5G	VM4P156A2GLG	VM4P156A2R1G	VM4P156A2R5G	VM4P155A2ERN
	M142	VM3P155A2GLG	VM3P155A2R1G	VM3P155A2R5G	VM4P155A2GLG	VM4P155A2R1G	VM4P155A2R5G	VM4P170A2ERN		
175	M137	3/4"	Quad Tri 480	VM3P170A2GLG	VM3P170A2R1G	VM3P170A2R5G	VM4P170A2GLG	VM4P170A2R1G	VM4P170A2R5G	VM4P170A2ERN
				VM3P176A2GLG	VM3P176A2R1G	VM3P176A2R5G	VM4P176A2GLG	VM4P176A2R1G	VM4P176A2R5G	VM4P176A2ERN
	M152	VM3P175A2GLG	VM3P175A2R1G	VM3P175A2R5G	VM4P175A2GLG	VM4P175A2R1G	VM4P175A2R5G	VM4P175A2ERN		
200	M136	3/4"	Quad Tri 480	VM3P200A2GLG	VM3P200A2R1G	VM3P200A2R5G	VM4P200A2GLG	VM4P200A2R1G	VM4P200A2R5G	VM4P200A2ERN
				VM3P206A2GLG	VM3P206A2R1G	VM3P206A2R5G	VM4P206A2GLG	VM4P206A2R1G	VM4P206A2R5G	VM4P206A2ERN
				VM3P205A2GLG	VM3P205A2R1G	VM3P205A2R5G	VM4P205A2GLG	VM4P205A2R1G	VM4P205A2R5G	VM4P205A2ERN

VM 150 - 200 WATT METAL HALIDE PULSE FLEXIBLE PENDANT										
DESCRIPTION				5-1/2" OPTIC THREAD SIZE ^②			7-3/4" OPTIC THREAD SIZE ^②			
WATTS	ANSI	HUB SIZE ^③	VOLTAGE ^④	GLOBE & GUARD	TYPE I GLASS REFRACTOR & GUARD	TYPE V GLASS REFRACTOR & GUARD	GLOBE & GUARD	TYPE I GLASS REFRACTOR & GUARD	TYPE V GLASS REFRACTOR & GUARD	ENCLOSED REFLECTOR
150	M102	3/4"	Quad Tri 480	VM3P150F2GLG	VM3P150F2R1G	VM3P150F2R5G	VM4P150F2GLG	VM4P150F2R1G	VM4P150F2R5G	VM4P156F2ERN
				VM3P156F2GLG	VM3P156F2R1G	VM3P156F2R5G	VM4P156F2GLG	VM4P156F2R1G	VM4P156F2R5G	VM4P155F2ERN
	M142	VM3P155F2GLG	VM3P155F2R1G	VM3P155F2R5G	VM4P155F2GLG	VM4P155F2R1G	VM4P155F2R5G	VM4P170F2ERN		
175	M137	3/4"	Quad Tri 480	VM3P170F2GLG	VM3P170F2R1G	VM3P170F2R5G	VM4P170F2GLG	VM4P170F2R1G	VM4P170F2R5G	VM4P170F2ERN
				VM3P176F2GLG	VM3P176F2R1G	VM3P176F2R5G	VM4P176F2GLG	VM4P176F2R1G	VM4P176F2R5G	VM4P176F2ERN
	M152	VM3P175F2GLG	VM3P175F2R1G	VM3P175F2R5G	VM4P175F2GLG	VM4P175F2R1G	VM4P175F2R5G	VM4P175F2ERN		
200	M136	3/4"	Quad Tri 480	VM3P200F2GLG	VM3P200F2R1G	VM3P200F2R5G	VM4P200F2GLG	VM4P200F2R1G	VM4P200F2R5G	VM4P200F2ERN
				VM3P206F2GLG	VM3P206F2R1G	VM3P206F2R5G	VM4P206F2GLG	VM4P206F2R1G	VM4P206F2R5G	VM4P206F2ERN
				VM3P205F2GLG	VM3P205F2R1G	VM3P205F2R5G	VM4P205F2GLG	VM4P205F2R1G	VM4P205F2R5G	VM4P205F2ERN

① See hazardous application data on pages L131 - L140 for limitations.

② Catalog numbers shown are with guard (except enclosed reflector); to omit guard change ending G to N; e.g. VM3P150A2GLN

③ Catalog numbers shown are with 3/4" conduit openings; change 2 to 3 for 1"; e.g. VM3P150A3GLG.

④ Consult catalog logic for other available voltages.

⑤ Add suffix NR for restricted breathing; see page L84 for more information.



METAL HALIDE PULSE, 150-200W MOGUL BASE HID



Ceiling
w/ 5-1/2"
Globe & Guard



Wall
w/ 5-1/2"
Refractor & Guard



Ceiling
w/ 7-3/4"
Globe & Guard



Wall
w/ 7-3/4"
Refractor & Guard



Ceiling
w/ Enclosed Reflector

VM 150 - 200 WATT METAL HALIDE PULSE CEILING										
DESCRIPTION				5-1/2" OPTIC THREAD SIZE ②			7-3/4" OPTIC THREAD SIZE ②			
WATTS	ANSI	HUB SIZE ③	VOLTAGE ④	GLOBE & GUARD	TYPE I GLASS REFRACTOR & GUARD	TYPE V GLASS REFRACTOR & GUARD	GLOBE & GUARD	TYPE I GLASS REFRACTOR & GUARD	TYPE V GLASS REFRACTOR & GUARD	ENCLOSED REFLECTOR
150	M102	3/4"	Quad Tri 480	VM3P150X2GLG	VM3P150X2R1G	VM3P150X2R5G	VM4P150X2GLG	VM4P150X2R1G	VM4P150X2R5G	VM4P150X2ERN
				VM3P156X2GLG	VM3P156X2R1G	VM3P156X2R5G	VM4P156X2GLG	VM4P156X2R1G	VM4P156X2R5G	VM4P156X2ERN
	M142	VM3P155X2GLG	VM3P155X2R1G	VM3P155X2R5G	VM4P155X2GLG	VM4P155X2R1G	VM4P155X2R5G	VM4P155X2ERN		
175	M137	3/4"	Quad Tri 480	VM3P170X2GLG	VM3P170X2R1G	VM3P170X2R5G	VM4P170X2GLG	VM4P170X2R1G	VM4P170X2R5G	VM4P170X2ERN
				VM3P176X2GLG	VM3P176X2R1G	VM3P176X2R5G	VM4P176X2GLG	VM4P176X2R1G	VM4P176X2R5G	VM4P176X2ERN
	M152	VM3P175X2GLG	VM3P175X2R1G	VM3P175X2R5G	VM4P175X2GLG	VM4P175X2R1G	VM4P175X2R5G	VM4P175X2ERN		
200	M136	3/4"	Quad Tri 480	VM3P200X2GLG	VM3P200X2R1G	VM3P200X2R5G	VM4P200X2GLG	VM4P200X2R1G	VM4P200X2R5G	VM4P200X2ERN
				VM3P206X2GLG	VM3P206X2R1G	VM3P206X2R5G	VM4P206X2GLG	VM4P206X2R1G	VM4P206X2R5G	VM4P206X2ERN
				VM3P205X2GLG	VM3P205X2R1G	VM3P205X2R5G	VM4P205X2GLG	VM4P205X2R1G	VM4P205X2R5G	VM4P205X2ERN

VM 150 - 200 WATT METAL HALIDE PULSE WALL										
DESCRIPTION				5-1/2" OPTIC THREAD SIZE ②			7-3/4" OPTIC THREAD SIZE ②			
WATTS	ANSI	HUB SIZE ③	VOLTAGE ④	GLOBE & GUARD	TYPE I GLASS REFRACTOR & GUARD	TYPE V GLASS REFRACTOR & GUARD	GLOBE & GUARD	TYPE I GLASS REFRACTOR & GUARD	TYPE V GLASS REFRACTOR & GUARD	ENCLOSED REFLECTOR
150	M102	3/4"	Quad Tri 480	VM3P150B2GLG	VM3P150B2R1G	VM3P150B2R5G	VM4P150B2GLG	VM4P150B2R1G	VM4P150B2R5G	VM4P150B2ERN
				VM3P156B2GLG	VM3P156B2R1G	VM3P156B2R5G	VM4P156B2GLG	VM4P156B2R1G	VM4P156B2R5G	VM4P156B2ERN
	M142	VM3P155B2GLG	VM3P155B2R1G	VM3P155B2R5G	VM4P155B2GLG	VM4P155B2R1G	VM4P155B2R5G	VM4P155B2ERN		
175	M137	3/4"	Quad Tri 480	VM3P170B2GLG	VM3P170B2R1G	VM3P170B2R5G	VM4P170B2GLG	VM4P170B2R1G	VM4P170B2R5G	VM4P170B2ERN
				VM3P176B2GLG	VM3P176B2R1G	VM3P176B2R5G	VM4P176B2GLG	VM4P176B2R1G	VM4P176B2R5G	VM4P176B2ERN
	M152	VM3P175B2GLG	VM3P175B2R1G	VM3P175B2R5G	VM4P175B2GLG	VM4P175B2R1G	VM4P175B2R5G	VM4P175B2ERN		
200	M136	3/4"	Quad Tri 480	VM3P200B2GLG	VM3P200B2R1G	VM3P200B2R5G	VM4P200B2GLG	VM4P200B2R1G	VM4P200B2R5G	VM4P200B2ERN
				VM3P206B2GLG	VM3P206B2R1G	VM3P206B2R5G	VM4P206B2GLG	VM4P206B2R1G	VM4P206B2R5G	VM4P206B2ERN
				VM3P205B2GLG	VM3P205B2R1G	VM3P205B2R5G	VM4P205B2GLG	VM4P205B2R1G	VM4P205B2R5G	VM4P205B2ERN

① See hazardous application data on pages L131 - L140 for limitations.

② Catalog numbers shown are with guard (except enclosed reflectors); to omit guard, change ending G to N; e.g. VM3P050X2GLN


③ Catalog numbers shown are with 3/4" conduit openings, change 2 to 3 for 1"; e.g. VM3P150X3GLG.

④ Consult catalog logic for other available voltages.

⑤ Add suffix NR for restricted breathing; see page L84 for more information.



METAL HALIDE PULSE, 150-200W MOGUL BASE HID



VM 150 - 200 WATT METAL HALIDE PULSE CONE										
DESCRIPTION				5-1/2" OPTIC THREAD SIZE ②			7-3/4" OPTIC THREAD SIZE ②			
WATTS	ANSI	HUB SIZE ③	VOLTAGE ④	GLOBE & GUARD	TYPE I GLASS REFRACTOR & GUARD	TYPE V GLASS REFRACTOR & GUARD	GLOBE & GUARD	TYPE I GLASS REFRACTOR & GUARD	TYPE V GLASS REFRACTOR & GUARD	ENCLOSED REFLECTOR
150	M102	3/4"	Quad Tri 480	VM3P150C2GLG	VM3P150C2R1G	VM3P150C2R5G	VM4P150C2GLG	VM4P150C2R1G	VM4P150C2R5G	VM4P150C2ERN
	M142			VM3P156C2GLG	VM3P156C2R1G	VM3P156C2R5G	VM4P156C2GLG	VM4P156C2R1G	VM4P156C2R5G	VM4P156C2ERN
				VM3P155C2GLG	VM3P155C2R1G	VM3P155C2R5G	VM4P155C2GLG	VM4P155C2R1G	VM4P155C2R5G	VM4P155C2ERN
175	M137	3/4"	Quad Tri 480	VM3P170C2GLG	VM3P170C2R1G	VM3P170C2R5G	VM4P170C2GLG	VM4P170C2R1G	VM4P170C2R5G	VM4P170C2ERN
	M152			VM3P176C2GLG	VM3P176C2R1G	VM3P176C2R5G	VM4P176C2GLG	VM4P176C2R1G	VM4P176C2R5G	VM4P176C2ERN
				VM3P175C2GLG	VM3P175C2R1G	VM3P175C2R5G	VM4P175C2GLG	VM4P175C2R1G	VM4P175C2R5G	VM4P175C2ERN
200	M136	3/4"	Quad Tri 480	VM3P200C2GLG	VM3P200C2R1G	VM3P200C2R5G	VM4P200C2GLG	VM4P200C2R1G	VM4P200C2R5G	VM4P200C2ERN
				VM3P206C2GLG	VM3P206C2R1G	VM3P206C2R5G	VM4P206C2GLG	VM4P206C2R1G	VM4P206C2R5G	VM4P206C2ERN
				VM3P205C2GLG	VM3P205C2R1G	VM3P205C2R5G	VM4P205C2GLG	VM4P205C2R1G	VM4P205C2R5G	VM4P205C2ERN

VM 150 - 200 WATT METAL HALIDE PULSE EZ ADAPTER										
DESCRIPTION				5-1/2" OPTIC THREAD SIZE ②			7-3/4" OPTIC THREAD SIZE ②			
WATTS	ANSI	HUB SIZE ③	VOLTAGE ④	GLOBE & GUARD	TYPE I GLASS REFRACTOR & GUARD	TYPE V GLASS REFRACTOR & GUARD	GLOBE & GUARD	TYPE I GLASS REFRACTOR & GUARD	TYPE V GLASS REFRACTOR & GUARD	ENCLOSED REFLECTOR
150	M102	⑥	Quad Tri 480	VM3P150EZGLG	VM3P150EZR1G	VM3P150EZR5G	VM4P150EZGLG	VM4P150EZR1G	VM4P150EZR5G	VM4P150EZERN
	M142			VM3P156EZGLG	VM3P156EZR1G	VM3P156EZR5G	VM4P156EZGLG	VM4P156EZR1G	VM4P156EZR5G	VM4P156EZERN
				VM3P155EZGLG	VM3P155EZR1G	VM3P155EZR5G	VM4P155EZGLG	VM4P155EZR1G	VM4P155EZR5G	VM4P155EZERN
175	M137	⑥	Quad Tri 480	VM3P170EZGLG	VM3P170EZR1G	VM3P170EZR5G	VM4P170EZGLG	VM4P170EZR1G	VM4P170EZR5G	VM4P170EZERN
	M152			VM3P176EZGLG	VM3P176EZR1G	VM3P176EZR5G	VM4P176EZGLG	VM4P176EZR1G	VM4P176EZR5G	VM4P176EZERN
				VM3P175EZGLG	VM3P175EZR1G	VM3P175EZR5G	VM4P175EZGLG	VM4P175EZR1G	VM4P175EZR5G	VM4P175EZERN
200	M136	⑥	Quad Tri 480	VM3P200EZGLG	VM3P200EZR1G	VM3P200EZR5G	VM4P200EZGLG	VM4P200EZR1G	VM4P200EZR5G	VM4P200EZERN
				VM3P206EZGLG	VM3P206EZR1G	VM3P206EZR5G	VM4P206EZGLG	VM4P206EZR1G	VM4P206EZR5G	VM4P206EZERN
				VM3P205EZGLG	VM3P205EZR1G	VM3P205EZR5G	VM4P205EZGLG	VM4P205EZR1G	VM4P205EZR5G	VM4P205EZERN

① See hazardous application data on pages L131 - L140 for limitations.
 ② Catalog numbers shown are with guard (except enclosed reflector); to omit guard change ending G to N; e.g. VM3P150C2GLN
 ③ Catalog numbers shown are with 3/4" conduit openings; change 2 to 3 for 1"; e.g. VM3P150C3GLG.
 ④ Consult catalog logic for other available voltages.
 ⑤ Add suffix NR for restricted breathing; see page L84 for more information.
 ⑥ VMEZA tank adapters UL "Classified" as an assembly for use between VM Tanks and EZ mounts. Order EZ mounts separately, see page L83.



METAL HALIDE PULSE, 150-200W MOGUL BASE HID



Stanchion 25°
w/ 5-1/2"
Globe & Guard



Stanchion Straight
w/ 5-1/2"
Refractor & Guard



Stanchion 25°
w/ 7-3/4"
Globe & Guard



Stanchion Straight
w/ 7-3/4"
Refractor & Guard



Stanchion 25°
w/ Enclosed Reflector

VM 150 - 200 WATT METAL HALIDE PULSE STANCHION 25° ANGLE

DESCRIPTION				5-1/2" OPTIC THREAD SIZE ②			7-3/4" OPTIC THREAD SIZE ②			
WATTS	ANSI	HUB SIZE ③	VOLTAGE ④	GLOBE & GUARD	TYPE I GLASS REFRACTOR & GUARD	TYPE V GLASS REFRACTOR & GUARD	GLOBE & GUARD	TYPE I GLASS REFRACTOR & GUARD	TYPE V GLASS REFRACTOR & GUARD	ENCLOSED REFLECTOR
150	M102 M142	1-1/2"	Quad Tri 480	VM3P150D5GLG	VM3P150D5R1G	VM3P150D5R5G	VM4P150D5GLG	VM4P150D5R1G	VM4P150D5R5G	VM4P150D5ERN
				VM3P156D5GLG	VM3P156D5R1G	VM3P156D5R5G	VM4P156D5GLG	VM4P156D5R1G	VM4P156D5R5G	VM4P156D5ERN
				VM3P155D5GLG	VM3P155D5R1G	VM3P155D5R5G	VM4P155D5GLG	VM4P155D5R1G	VM4P155D5R5G	VM4P155D5ERN
175	M137 M152	1-1/2"	Quad Tri 480	VM3P170D5GLG	VM3P170D5R1G	VM3P170D5R5G	VM4P170D5GLG	VM4P170D5R1G	VM4P170D5R5G	VM4P170D5ERN
				VM3P176D5GLG	VM3P176D5R1G	VM3P176D5R5G	VM4P176D5GLG	VM4P176D5R1G	VM4P176D5R5G	VM4P176D5ERN
				VM3P175D5GLG	VM3P175D5R1G	VM3P175D5R5G	VM4P175D5GLG	VM4P175D5R1G	VM4P175D5R5G	VM4P175D5ERN
200	M136	1-1/2"	Quad Tri 480	VM3P200D5GLG	VM3P200D5R1G	VM3P200D5R5G	VM4P200D5GLG	VM4P200D5R1G	VM4P200D5R5G	VM4P200D5ERN
				VM3P206D5GLG	VM3P206D5R1G	VM3P206D5R5G	VM4P206D5GLG	VM4P206D5R1G	VM4P206D5R5G	VM4P206D5ERN
				VM3P205D5GLG	VM3P205D5R1G	VM3P205D5R5G	VM4P205D5GLG	VM4P205D5R1G	VM4P205D5R5G	VM4P205D5ERN

VM 150 - 200 WATT METAL HALIDE PULSE STANCHION STRAIGHT

DESCRIPTION				5-1/2" OPTIC THREAD SIZE ②			7-3/4" OPTIC THREAD SIZE ②			
WATTS	ANSI	HUB SIZE ③	VOLTAGE ④	GLOBE & GUARD	TYPE I GLASS REFRACTOR & GUARD	TYPE V GLASS REFRACTOR & GUARD	GLOBE & GUARD	TYPE I GLASS REFRACTOR & GUARD	TYPE V GLASS REFRACTOR & GUARD	ENCLOSED REFLECTOR
150	M102 M142	1-1/2"	Quad Tri 480	VM3P150S5GLG	VM3P150S5R1G	VM3P150S5R5G	VM4P150S5GLG	VM4P150S5R1G	VM4P150S5R5G	VM4P150S5ERN
				VM3P156S5GLG	VM3P156S5R1G	VM3P156S5R5G	VM4P156S5GLG	VM4P156S5R1G	VM4P156S5R5G	VM4P156S5ERN
				VM3P155S5GLG	VM3P155S5R1G	VM3P155S5R5G	VM4P155S5GLG	VM4P155S5R1G	VM4P155S5R5G	VM4P155S5ERN
175	M137 M152	1-1/2"	Quad Tri 480	VM3P170S5GLG	VM3P170S5R1G	VM3P170S5R5G	VM4P170S5GLG	VM4P170S5R1G	VM4P170S5R5G	VM4P170S5ERN
				VM3P176S5GLG	VM3P176S5R1G	VM3P176S5R5G	VM4P176S5GLG	VM4P176S5R1G	VM4P176S5R5G	VM4P176S5ERN
				VM3P175S5GLG	VM3P175S5R1G	VM3P175S5R5G	VM4P175S5GLG	VM4P175S5R1G	VM4P175S5R5G	VM4P175S5ERN
200	M136	1-1/2"	Quad Tri 480	VM3P200S5GLG	VM3P200S5R1G	VM3P200S5R5G	VM4P200S5GLG	VM4P200S5R1G	VM4P200S5R5G	VM4P200S5ERN
				VM3P206S5GLG	VM3P206S5R1G	VM3P206S5R5G	VM4P206S5GLG	VM4P206S5R1G	VM4P206S5R5G	VM4P206S5ERN
				VM3P205S5GLG	VM3P205S5R1G	VM3P205S5R5G	VM4P205S5GLG	VM4P205S5R1G	VM4P205S5R5G	VM4P205S5ERN

① See hazardous application data on pages L131 - L140 for limitations.

② Catalog numbers shown are with guard (except enclosed reflectors); to omit guard change ending G to N; e.g. VM3P150D5GLN

③ Catalog numbers shown are with 1-1/2" conduit openings, change 5 to 4 for 1-1/4"; e.g. VM3P150D4GLG.

④ Consult catalog logic for other available voltages.

⑤ Add suffix NR for restricted breathing; see page L84 for more information.