



METAL HALIDE PULSE, 400W MOGUL BASE HID



Pendant
w/ Globe & Guard



Pendant
w/ Spin-Top
Refractor



Ceiling
w/ Enclosed Reflector

VM 250 - 400 WATT METAL HALIDE PULSE PENDANT							
DESCRIPTION				7-3/4" OPTIC THREAD SIZE ②			
WATTS	ANSI	HUB SIZE ③	VOLTAGE ④	GLOBE & GUARD	TYPE V SPIN-TOP GLASS REFRACTOR	ENCLOSED REFLECTOR	POLYCARBONATE SHIELDED ENCLOSED REFLECTOR
250	M138	3/4"	Quad Tri 480	VM5P250A2GLG	VM5P250A2S5N	VM5P250A2ERN	VM5P250A2EPN
	M153			VM5P256A2GLG	VM5P256A2S5N	VM5P256A2ERN	VM5P256A2EPN
				VM5P255A2GLG	VM5P255A2S5N	VM5P255A2ERN	VM5P255A2EPN
320	M132	3/4"	Quad Tri 480	VM5P320A2GLG	VM5P320A2S5N	VM5P320A2ERN	VM5P320A2EPN
	M154			VM5P326A2GLG	VM5P326A2S5N	VM5P326A2ERN	VM5P326A2EPN
				VM5P325A2GLG	VM5P325A2S5N	VM5P325A2ERN	VM5P325A2EPN
350	M131	3/4"	Quad Tri 480	VM5P350A2GLG	VM5P350A2S5N	VM5P350A2ERN	VM5P350A2EPN
				VM5P356A2GLG	VM5P356A2S5N	VM5P356A2ERN	VM5P356A2EPN
				VM5P355A2GLG	VM5P355A2S5N	VM5P355A2ERN	VM5P355A2EPN
400	M135 M155	3/4"	Quad Tri 480	VM5P400A2GLG	VM5P400A2S5N	VM5P400A2ERN	VM5P400A2EPN
				VM5P406A2GLG	VM5P406A2S5N	VM5P406A2ERN	VM5P406A2EPN
				VM5P405A2GLG	VM5P405A2S5N	VM5P405A2ERN	VM5P405A2EPN

VM 250 - 400 WATT METAL HALIDE PULSE CEILING							
DESCRIPTION				7-3/4" OPTIC THREAD SIZE ②			
WATTS	ANSI	HUB SIZE ③	VOLTAGE ④	GLOBE & GUARD	TYPE V SPIN-TOP GLASS REFRACTOR	ENCLOSED REFLECTOR	POLYCARBONATE SHIELDED ENCLOSED REFLECTOR
250	M138	3/4"	Quad Tri 480	VM5P250X2GLG	VM5P250X2S5N	VM5P250X2ERN	VM5P250X2EPN
	M153			VM5P256X2GLG	VM5P256X2S5N	VM5P256X2ERN	VM5P256X2EPN
				VM5P255X2GLG	VM5P255X2S5N	VM5P255X2ERN	VM5P255X2EPN
320	M132	3/4"	Quad Tri 480	VM5P320X2GLG	VM5P320X2S5N	VM5P320X2ERN	VM5P320X2EPN
	M154			VM5P326X2GLG	VM5P326X2S5N	VM5P326X2ERN	VM5P326X2EPN
				VM5P325X2GLG	VM5P325X2S5N	VM5P325X2ERN	VM5P325X2EPN
350	M131	3/4"	Quad Tri 480	VM5P350X2GLG	VM5P350X2S5N	VM5P350X2ERN	VM5P350X2EPN
				VM5P356X2GLG	VM5P356X2S5N	VM5P356X2ERN	VM5P356X2EPN
				VM5P355X2GLG	VM5P355X2S5N	VM5P355X2ERN	VM5P355X2EPN
400	M135 M155	3/4"	Quad Tri 480	VM5P400X2GLG	VM5P400X2S5N	VM5P400X2ERN	VM5P400X2EPN
				VM5P406X2GLG	VM5P406X2S5N	VM5P406X2ERN	VM5P406X2EPN
				VM5P405X2GLG	VM5P405X2S5N	VM5P405X2ERN	VM5P405X2EPN

① See hazardous application data on pages L131 - L140 for limitations.

② Globe catalog number shown with guard. To omit guard, change G to N; e.g. VM5P250A2GLN. Order spin top and enclosed reflector guards separately.

③ Catalog numbers shown are with 3/4" conduit openings, change 2 to 3 for 1"; e.g. VM5P250A3GLG.

④ Consult catalog logic for other available voltages.

⑤ Add suffix NR for restricted breathing; see page L84 for more information.



METAL HALIDE PULSE, 400W MOGUL BASE HID

Wall
w/ Globe & GuardWall
w/ Spin-Top
RefractorCone
w/ Enclosed Reflector

VM 250 - 400 WATT METAL HALIDE PULSE WALL							
DESCRIPTION				7-3/4" OPTIC THREAD SIZE ②			
WATTS	ANSI	HUB SIZE ③	VOLTAGE ④	GLOBE & GUARD	TYPE V SPIN-TOP GLASS REFRACTOR	ENCLOSED REFLECTOR	POLYCARBONATE SHIELDED ENCLOSED REFLECTOR
250	M138	3/4"	Quad Tri 480	VM5P250B2GLG	VM5P250B2S5N	VM5P250B2ERN	—
	M153			VM5P256B2GLG	VM5P256B2S5N	VM5P256B2ERN	—
				VM5P255B2GLG	VM5P255B2S5N	VM5P255B2ERN	—
320	M132	3/4"	Quad Tri 480	VM5P320B2GLG	VM5P320B2S5N	VM5P320B2ERN	—
	M154			VM5P326B2GLG	VM5P326B2S5N	VM5P326B2ERN	—
				VM5P325B2GLG	VM5P325B2S5N	VM5P325B2ERN	—
350	M131	3/4"	Quad Tri 480	VM5P350B2GLG	VM5P350B2S5N	VM5P350B2ERN	—
				VM5P356B2GLG	VM5P356B2S5N	VM5P356B2ERN	—
				VM5P355B2GLG	VM5P355B2S5N	VM5P355B2ERN	—
400	M135	3/4"	Quad Tri 480	VM5P400B2GLG	VM5P400B2S5N	VM5P400B2ERN	—
	M155			VM5P406B2GLG	VM5P406B2S5N	VM5P406B2ERN	—
				VM5P405B2GLG	VM5P405B2S5N	VM5P405B2ERN	—

VM 250 - 400 WATT METAL HALIDE PULSE CONE							
DESCRIPTION				7-3/4" OPTIC THREAD SIZE ②			
WATTS	ANSI	HUB SIZE ③	VOLTAGE ④	GLOBE & GUARD	TYPE V SPIN-TOP GLASS REFRACTOR	ENCLOSED REFLECTOR	POLYCARBONATE SHIELDED ENCLOSED REFLECTOR
250	M138	3/4"	Quad Tri 480	VM5P250C2GLG	VM5P250C2S5N	VM5P250C2ERN	VM5P250C2EPN
	M153			VM5P256C2GLG	VM5P256C2S5N	VM5P256C2ERN	VM5P256C2EPN
				VM5P255C2GLG	VM5P255C2S5N	VM5P255C2ERN	VM5P255C2EPN
320	M132	3/4"	Quad Tri 480	VM5P320C2GLG	VM5P320C2S5N	VM5P320C2ERN	VM5P320C2EPN
	M154			VM5P326C2GLG	VM5P326C2S5N	VM5P326C2ERN	VM5P326C2EPN
				VM5P325C2GLG	VM5P325C2S5N	VM5P325C2ERN	VM5P325C2EPN
350	M131	3/4"	Quad Tri 480	VM5P350C2GLG	VM5P350C2S5N	VM5P350C2ERN	VM5P350C2EPN
				VM5P356C2GLG	VM5P356C2S5N	VM5P356C2ERN	VM5P356C2EPN
				VM5P355C2GLG	VM5P355C2S5N	VM5P355C2ERN	VM5P355C2EPN
400	M135	3/4"	Quad Tri 480	VM5P400C2GLG	VM5P400C2S5N	VM5P400C2ERN	VM5P400C2EPN
	M155			VM5P406C2GLG	VM5P406C2S5N	VM5P406C2ERN	VM5P406C2EPN
				VM5P405C2GLG	VM5P405C2S5N	VM5P405C2ERN	VM5P405C2EPN

① See hazardous application data on pages L131 - L140 for limitations.

② Globe catalog number shown with guard. To omit guard, change G to N; e.g. VM5P250B2GLN. Order spin top and enclosed reflector guards separately.

③ Catalog numbers shown are with 3/4" conduit openings, change 2 to 3 for 1"; e.g. VM5P250B3GLG.

④ Consult catalog logic for other available voltages.

⑤ Add suffix NR for restricted breathing; see page L84 for more information.



METAL HALIDE PULSE, 250-400 W MOGUL BASE HID



**Stanchion 25°
w/ Globe & Guard**



**Stanchion 25°
w/ Spin-Top
Refractor**



**Stanchion Straight
w/ Enclosed Reflector**

Class I, Div. 2, Groups A,B,C,D
Class I, Zone 2, Groups IIC, IIB, IIA
Class II, Div. 1 & 2, Groups E,F,G
Class III
Suitable for wet locations
NEMA 3, 4, 4X
IP66

UL US LISTED - File E10514 (Hazardous & Marine)

SP US Certified - File LR11713

NR Restricted Breathing Option

Class I, Zone 2 AEx nAnR
Class I, Zone 2 Ex nR

VM 250 - 400 WATT METAL HALIDE PULSE STANCHION 25° ANGLE						
DESCRIPTION				7-3/4" OPTIC THREAD SIZE		
WATTS	ANSI	HUB SIZE	VOLTAGE	GLOBE & GUARD	TYPE V SPIN-TOP GLASS REFRACTOR	ENCLOSED REFLECTOR
250	M138	1-1/2"	Quad Tri 480	VM5P250D5GLG	VM5P250D5S5N	VM5P250D5ERN
	M153			VM5P256D5GLG	VM5P256D5S5N	VM5P256D5ERN
				VM5P255D5GLG	VM5P255D5S5N	VM5P255D5ERN
320	M132	1-1/2"	Quad Tri 480	VM5P320D5GLG	VM5P320D5S5N	VM5P320D5ERN
	M154			VM5P326D5GLG	VM5P326D5S5N	VM5P326D5ERN
				VM5P325D5GLG	VM5P325D5S5N	VM5P325D5ERN
350	M131	1-1/2"	Quad Tri 480	VM5P350D5GLG	VM5P350D5S5N	VM5P350D5ERN
				VM5P356D5GLG	VM5P356D5S5N	VM5P356D5ERN
				VM5P355D5GLG	VM5P355D5S5N	VM5P355D5ERN
400	M135	1-1/2"	Quad Tri 480	VM5P400D5GLG	VM5P400D5S5N	VM5P400D5ERN
	M155			VM5P406D5GLG	VM5P406D5S5N	VM5P406D5ERN
				VM5P405D5GLG	VM5P405D5S5N	VM5P405D5ERN

VM 250 - 400 WATT METAL HALIDE PULSE STANCHION STRAIGHT						
DESCRIPTION				7-3/4" OPTIC THREAD SIZE		
WATTS	ANSI	HUB SIZE	VOLTAGE	GLOBE & GUARD	TYPE V SPIN-TOP GLASS REFRACTOR	ENCLOSED REFLECTOR
250	M138	1-1/2"	Quad Tri 480	VM5P250S5GLG	VM5P250S5S5N	VM5P250S5ERN
	M153			VM5P256S5GLG	VM5P256S5S5N	VM5P256S5ERN
				VM5P255S5GLG	VM5P255S5S5N	VM5P255S5ERN
320	M132	1-1/2"	Quad Tri 480	VM5P320S5GLG	VM5P320S5S5N	VM5P320S5ERN
	M154			VM5P326S5GLG	VM5P326S5S5N	VM5P326S5ERN
				VM5P325S5GLG	VM5P325S5S5N	VM5P325S5ERN
350	M131	1-1/2"	Quad Tri 480	VM5P350S5GLG	VM5P350S5S5N	VM5P350S5ERN
				VM5P356S5GLG	VM5P356S5S5N	VM5P356S5ERN
				VM5P355S5GLG	VM5P355S5S5N	VM5P355S5ERN
400	M135	1-1/2"	Quad Tri 480	VM5P400S5GLG	VM5P400S5S5N	VM5P400S5ERN
	M155			VM5P406S5GLG	VM5P406S5S5N	VM5P406S5ERN
				VM5P405S5GLG	VM5P405S5S5N	VM5P405S5ERN

① See hazardous application data on pages L131 - L140 for limitations.

② Globe catalog number shown with guard. To omit guard, change G to N; e.g. VM5P250D5GLN. Order spin top and enclosed reflector guards separately.

③ Catalog numbers shown with 1-1/2" conduit openings; change 5 to 4 for 1-1/4"; e.g. VM5P250D4GLG.

④ Consult catalog logic for other available voltages.

⑤ Add suffix NR for restricted breathing; see page L84 for more information.

LIGHTING

CERTILITE® V SERIES



METAL HALIDE PULSE, 250-400W MOGUL BASE HID



EZ Adapter w/ Globe & Guard



EZ Adapter w/ Spin-Top Refractor



EZ Adapter w/ Enclosed Reflector

VM 250 - 400 WATT METAL HALIDE PULSE EZ ADAPTER								
DESCRIPTION				7-3/4" OPTIC THREAD SIZE ②				
WATTS	ANSI	HUB SIZE ③	VOLTAGE ④	GLOBE & GUARD	TYPE V SPIN-TOP GLASS REFRACTOR	ENCLOSED REFLECTOR	"POLYCARBONATE SHIELDED ENCLOSED REFLECTOR O	
250	M138	3/4"	Quad Tri 480	VM5P250EZGLG	VM5P250EZS5N	VM5P250EZERN	VM5P250EZEPN	
	M153			VM5P256EZGLG	VM5P256EZS5N	VM5P256EZERN	VM5P256EZEPN	
				VM5P255EZGLG	VM5P255EZS5N	VM5P255EZERN	VM5P255EZEPN	
320	M132	3/4"	Quad Tri 480	VM5P320EZGLG	VM5P320EZS5N	VM5P320EZERN	VM5P320EZEPN	
	M154			VM5P326EZGLG	VM5P326EZS5N	VM5P326EZERN	VM5P326EZEPN	
				VM5P325EZGLG	VM5P325EZS5N	VM5P325EZERN	VM5P325EZEPN	
350	M131	3/4"	Quad Tri 480	VM5P350EZGLG	VM5P350EZS5N	VM5P350EZERN	VM5P350EZEPN	
					VM5P356EZGLG	VM5P356EZS5N	VM5P356EZERN	VM5P356EZEPN
					VM5P355EZGLG	VM5P355EZS5N	VM5P355EZERN	VM5P355EZEPN
400	M135	3/4"	Quad Tri 480	VM5P400EZGLG	VM5P400EZS5N	VM5P400EZERN	VM5P400EZEPN	
	M155			VM5P406EZGLG	VM5P406EZS5N	VM5P406EZERN	VM5P406EZEPN	
					VM5P405EZGLG	VM5P405EZS5N	VM5P405EZERN	VM5P405EZEPN



Pendant



Ceiling



Wall Bracket



25° Stanchion

MOUNTING BOXES				
CATALOG NUMBER				HUB SIZE
PENDANT	CEILING	BRACKET	STANCHION	
EZA2	EZX2	EZB2	—	3/4"
EZA3	EZX3	EZB3	—	1"
—	—	—	EZD4A*	1-1/4"/1-1/2"*

*1-1/2" furnished with 1-1/2"-1-1/4" reducer and extension. Extension only part number EZDVMA.

① See hazardous application data on pages L131 - L140 for limitations.

② Globe catalog number shown with guard. To omit guard, change G to N; e.g. VM5P250EZGLN. Order spin top and enclosed reflector guards separately.

③ VMEZA tank adapters UL "classified" as an assembly for use between VM tanks and EZ mounts. See above for separate ordering information.

④ Consult catalog logic for other available voltages.

⑤ Add suffix NR for restricted breathing; see page L84 for more information.

⑥ VMEP40 not for use with EZ wall bracket.