



HIGH PRESSURE SODIUM, 35-150W MEDIUM BASE HID



VM1 Pendant
w/ 5-1/2"
Globe & Guard



VM2 Pendant
w/ 7-3/4"
Globe & Guard



VM1 Flexible Pendant
w/ 5-1/2"
Reflector & Guard



VM2 Flexible Pendant
w/ 7-3/4"
Reflector & Guard

Class I, Div. 2, Groups A,B,C,D^①
Class I, Zone 2, Groups IIC, IIB, IIA
Class II, Div. 1 & 2, Groups E,F,G
Class III
Suitable for wet locations
NEMA 3, 4, 4X
IP66

UL LISTED - File E10514 (Hazardous & Marine)

CSA Certified - File LR11713

NR Restricted Breathing Option^⑤
Class I, Zone 2 AEx nAnR **CSA**
Class I, Zone 2 Ex nR **CSA**

VM 35 - 150 HIGH PRESSURE SODIUM - PENDANT										
DESCRIPTION				5-1/2" OPTIC THREAD SIZE ②			7-3/4" OPTIC THREAD SIZE ②			
WATTS	ANSI	HUB SIZE ③	VOLTAGE ④	GLOBE & GUARD	TYPE I GLASS REFRACTOR & GUARD	TYPE V GLASS REFRACTOR & GUARD	GLOBE & GUARD	TYPE I GLASS REFRACTOR & GUARD	TYPE V GLASS REFRACTOR & GUARD	12" SPIN-TOP TYPE V REFRACTOR & GUARD
35	S76	3/4"	120V	VM1S031A2GLG	VM1S031A2R1G	VM1S031A2R5G	VM2S031A2GLG	VM2S031A2R1G	VM2S031A2R5G	VM2S031A2S5G
50	S68	3/4"	Quad	VM1S050A2GLG	VM1S050A2R1G	VM1S050A2R5G	VM2S050A2GLG	VM2S050A2R1G	VM2S050A2R5G	VM2S050A2S5G
70	S62	3/4"	Quad Tri 480	VM1S070A2GLG	VM1S070A2R1G	VM1S070A2R5G	VM2S070A2GLG	VM2S070A2R1G	VM2S070A2R5G	VM2S070A2S5G
				VM1S076A2GLG	VM1S076A2R1G	VM1S076A2R5G	VM2S076A2GLG	VM2S076A2R1G	VM2S076A2R5G	VM2S076A2S5G
				VM1S075A2GLG	VM1S075A2R1G	VM1S075A2R5G	VM2S075A2GLG	VM2S075A2R1G	VM2S075A2R5G	VM2S075A2S5G
100	S54	3/4"	Quad Tri 480	VM1S100A2GLG	VM1S100A2R1G	VM1S100A2R5G	VM2S100A2GLG	VM2S100A2R1G	VM2S100A2R5G	VM2S100A2S5G
				VM1S106A2GLG	VM1S106A2R1G	VM1S106A2R5G	VM2S106A2GLG	VM2S106A2R1G	VM2S106A2R5G	VM2S106A2S5G
				VM1S105A2GLG	VM1S105A2R1G	VM1S105A2R5G	VM2S105A2GLG	VM2S105A2R1G	VM2S105A2R5G	VM2S105A2S5G
150	S55	3/4"	Quad Tri 480	VM1S150A2GLG	VM1S150A2R1G	VM1S150A2R5G	VM2S150A2GLG	VM2S150A2R1G	VM2S150A2R5G	VM2S150A2S5G
				VM1S156A2GLG	VM1S156A2R1G	VM1S156A2R5G	VM2S156A2GLG	VM2S156A2R1G	VM2S156A2R5G	VM2S156A2S5G
				VM1S155A2GLG	VM1S155A2R1G	VM1S155A2R5G	VM2S155A2GLG	VM2S155A2R1G	VM2S155A2R5G	VM2S155A2S5G

VM 35 - 150 HIGH PRESSURE SODIUM - FLEX PENDANT										
DESCRIPTION				5-1/2" OPTIC THREAD SIZE ②			7-3/4" OPTIC THREAD SIZE ②			
WATTS	ANSI	HUB SIZE ③	VOLTAGE ④	GLOBE & GUARD	TYPE I GLASS REFRACTOR & GUARD	TYPE V GLASS REFRACTOR & GUARD	GLOBE & GUARD	TYPE I GLASS REFRACTOR & GUARD	TYPE V GLASS REFRACTOR & GUARD	12" SPIN-TOP TYPE V REFRACTOR & GUARD
35	S76	3/4"	120V	VM1S031F2GLG	VM1S031F2R1G	VM1S031F2R5G	VM2S031F2GLG	VM2S031F2R1G	VM2S031F2R5G	VM2S031F2S5G
50	S68	3/4"	Quad	VM1S050F2GLG	VM1S050F2R1G	VM1S050F2R5G	VM2S050F2GLG	VM2S050F2R1G	VM2S050F2R5G	VM2S050F2S5G
70	S62	3/4"	Quad Tri 480	VM1S070F2GLG	VM1S070F2R1G	VM1S070F2R5G	VM2S070F2GLG	VM2S070F2R1G	VM2S070F2R5G	VM2S070F2S5G
				VM1S076F2GLG	VM1S076F2R1G	VM1S076F2R5G	VM2S076F2GLG	VM2S076F2R1G	VM2S076F2R5G	VM2S076F2S5G
				VM1S075F2GLG	VM1S075F2R1G	VM1S075F2R5G	VM2S075F2GLG	VM2S075F2R1G	VM2S075F2R5G	VM2S075F2S5G
100	S54	3/4"	Quad Tri 480	VM1S100F2GLG	VM1S100F2R1G	VM1S100F2R5G	VM2S100F2GLG	VM2S100F2R1G	VM2S100F2R5G	VM2S100F2S5G
				VM1S106F2GLG	VM1S106F2R1G	VM1S106F2R5G	VM2S106F2GLG	VM2S106F2R1G	VM2S106F2R5G	VM2S106F2S5G
				VM1S105F2GLG	VM1S105F2R1G	VM1S105F2R5G	VM2S105F2GLG	VM2S105F2R1G	VM2S105F2R5G	VM2S105F2S5G
150	S55	3/4"	Quad Tri 480	VM1S150F2GLG	VM1S150F2R1G	VM1S150F2R5G	VM2S150F2GLG	VM2S150F2R1G	VM2S150F2R5G	VM2S150F2S5G
				VM1S156F2GLG	VM1S156F2R1G	VM1S156F2R5G	VM2S156F2GLG	VM2S156F2R1G	VM2S156F2R5G	VM2S156F2S5G
				VM1S155F2GLG	VM1S155F2R1G	VM1S155F2R5G	VM2S155F2GLG	VM2S155F2R1G	VM2S155F2R5G	VM2S155F2S5G

① See hazardous location data pages L131- L140 for application suitability
 ② Catalog numbers shown are with Guard; to omit guard change ending G to N; e.g. VM1S050A2GLN
 ③ Catalog numbers shown are with 3/4" conduit openings; change "2" to "3" for 1" e.g. VM1S050A3GLG
 ④ Consult catalog logic for other available voltage & lamp combinations
 ⑤ Add suffix NR for AEx nR Restricted Breathing; see page L84 for more information (only)



LIGHTING

CERTILITE® V SERIES

HIGH PRESSURE SODIUM, 35-150W MEDIUM BASE HID



VM1 Ceiling
w/ 5-1/2"
Globe & Guard



VM2 Ceiling
w/ 7-3/4"
Globe & Guard



VM1 Wall
w/ 5-1/2"
Refractor & Guard



VM2 Wall
w/ 7-3/4"
Refractor & Guard

VM 35 - 150 HIGH PRESSURE SODIUM - CEILING										
DESCRIPTION				5-1/2" OPTIC THREAD SIZE ②			7-3/4" OPTIC THREAD SIZE ②			
WATTS	ANSI	HUB SIZE ③	VOLTAGE ④	GLOBE & GUARD	TYPE I GLASS REFRACTOR & GUARD	TYPE V GLASS REFRACTOR & GUARD	GLOBE & GUARD	TYPE I GLASS REFRACTOR & GUARD	TYPE V GLASS REFRACTOR & GUARD	12" SPIN-TOP TYPE V REFRACTOR & GUARD
35	S76	3/4"	120V	VM1S031X2GLG	VM1S031X2R1G	VM1S031X2R5G	VM2S031X2GLG	VM2S031X2R1G	VM2S031X2R5G	VM2S031X2S5G
50	S68	3/4"	Quad	VM1S050X2GLG	VM1S050X2R1G	VM1S050X2R5G	VM2S050X2GLG	VM2S050X2R1G	VM2S050X2R5G	VM2S050X2S5G
70	S62	3/4"	Quad Tri 480	VM1S070X2GLG	VM1S070X2R1G	VM1S070X2R5G	VM2S070X2GLG	VM2S070X2R1G	VM2S070X2R5G	VM2S070X2S5G
				VM1S076X2GLG	VM1S076X2R1G	VM1S076X2R5G	VM2S076X2GLG	VM2S076X2R1G	VM2S076X2R5G	VM2S076X2S5G
				VM1S075X2GLG	VM1S075X2R1G	VM1S075X2R5G	VM2S075X2GLG	VM2S075X2R1G	VM2S075X2R5G	VM2S075X2S5G
100	S54	3/4"	Quad Tri 480	VM1S100X2GLG	VM1S100X2R1G	VM1S100X2R5G	VM2S100X2GLG	VM2S100X2R1G	VM2S100X2R5G	VM2S100X2S5G
				VM1S106X2GLG	VM1S106X2R1G	VM1S106X2R5G	VM2S106X2GLG	VM2S106X2R1G	VM2S106X2R5G	VM2S106X2S5G
				VM1S105X2GLG	VM1S105X2R1G	VM1S105X2R5G	VM2S105X2GLG	VM2S105X2R1G	VM2S105X2R5G	VM2S105X2S5G
150	S55	3/4"	Quad Tri 480	VM1S150X2GLG	VM1S150X2R1G	VM1S150X2R5G	VM2S150X2GLG	VM2S150X2R1G	VM2S150X2R5G	VM2S150X2S5G
				VM1S156X2GLG	VM1S156X2R1G	VM1S156X2R5G	VM2S156X2GLG	VM2S156X2R1G	VM2S156X2R5G	VM2S156X2S5G
				VM1S155X2GLG	VM1S155X2R1G	VM1S155X2R5G	VM2S155X2GLG	VM2S155X2R1G	VM2S155X2R5G	VM2S155X2S5G

VM 35 - 150 HIGH PRESSURE SODIUM - WALL										
DESCRIPTION				5-1/2" OPTIC THREAD SIZE ②			7-3/4" OPTIC THREAD SIZE ②			
WATTS	ANSI	HUB SIZE ③	VOLTAGE ④	GLOBE & GUARD	TYPE I GLASS REFRACTOR & GUARD	TYPE V GLASS REFRACTOR & GUARD	GLOBE & GUARD	TYPE I GLASS REFRACTOR & GUARD	TYPE V GLASS REFRACTOR & GUARD	12 SPIN-TOP TYPE V REFRACTOR & GUARD
35	S76	3/4"	120V	VM1S031B2GLG	VM1S031B2R1G	VM1S031B2R5G	VM2S031B2GLG	VM2S031B2R1G	VM2S031B2R5G	VM2S031B2S5G
50	S68	3/4"	Quad	VM1S050B2GLG	VM1S050B2R1G	VM1S050B2R5G	VM2S050B2GLG	VM2S050B2R1G	VM2S050B2R5G	VM2S050B2S5G
70	S62	3/4"	Quad Tri 480	VM1S070B2GLG	VM1S070B2R1G	VM1S070B2R5G	VM2S070B2GLG	VM2S070B2R1G	VM2S070B2R5G	VM2S070B2S5G
				VM1S076B2GLG	VM1S076B2R1G	VM1S076B2R5G	VM2S076B2GLG	VM2S076B2R1G	VM2S076B2R5G	VM2S076B2S5G
				VM1S075B2GLG	VM1S075B2R1G	VM1S075B2R5G	VM2S075B2GLG	VM2S075B2R1G	VM2S075B2R5G	VM2S075B2S5G
100	S54	3/4"	Quad Tri 480	VM1S100B2GLG	VM1S100B2R1G	VM1S100B2R5G	VM2S100B2GLG	VM2S100B2R1G	VM2S100B2R5G	VM2S100B2S5G
				VM1S106B2GLG	VM1S106B2R1G	VM1S106B2R5G	VM2S106B2GLG	VM2S106B2R1G	VM2S106B2R5G	VM2S106B2S5G
				VM1S105B2GLG	VM1S105B2R1G	VM1S105B2R5G	VM2S105B2GLG	VM2S105B2R1G	VM2S105B2R5G	VM2S105B2S5G
150	S55	3/4"	Quad Tri 480	VM1S150B2GLG	VM1S150B2R1G	VM1S150B2R5G	VM2S150B2GLG	VM2S150B2R1G	VM2S150B2R5G	VM2S150B2S5G
				VM1S156B2GLG	VM1S156B2R1G	VM1S156B2R5G	VM2S156B2GLG	VM2S156B2R1G	VM2S156B2R5G	VM2S156B2S5G
				VM1S155B2GLG	VM1S155B2R1G	VM1S155B2R5G	VM2S155B2GLG	VM2S155B2R1G	VM2S155B2R5G	VM2S155B2S5G

① See hazardous location data pages L131 - L140 for application suitability
 ② Catalog numbers shown are with Guard; to omit guard change ending G to N; e.g. VM1S050X2GLN
 ③ Catalog numbers shown are with 3/4" conduit openings; change "2" to "3" for 1" e.g. VM1S050X3GLG
 ④ Consult catalog logic for other available voltage & lamp combinations
 ⑤ Add suffix NR for AEx nR Restricted Breathing; see page L84 for more information (cULus only)



CERTILITE® V SERIES

KILLARK

HIGH PRESSURE SODIUM, 35-150W MEDIUM BASE HID



**VM1 Cone
w/5-1/2"
Globe & Guard**



**VM2 Cone
w/7-3/4"
Globe & Guard**



**VM1 EZ Adapter
w/5-1/2"
Refractor & Guard**



**VM2 EZ Adapter
w/7-3/4"
Refractor & Guard**

VM 35 - 150 HIGH PRESSURE SODIUM -CONE										
DESCRIPTION				5-1/2" OPTIC THREAD SIZE ②			7-3/4" OPTIC THREAD SIZE ②			
WATTS	ANSI	HUB SIZE③	VOLTAGE ④	GLOBE & GUARD	TYPE I GLASS REFRACTOR & GUARD	TYPE V GLASS REFRACTOR & GUARD	GLOBE & GUARD	TYPE I GLASS REFRACTOR & GUARD	TYPE V GLASS REFRACTOR & GUARD	12" SPIN-TOP TYPE V REFRACTOR & GUARD
35	S76	3/4	120V	VM1S031C2GLG	VM1S031C2R1G	VM1S031C2R5G	VM2S031C2GLG	VM2S031C2R1G	VM2S031C2R5G	VM2S031C2S5G
50	S68	3/4	Quad	VM1S050C2GLG	VM1S050C2R1G	VM1S050C2R5G	VM2S050C2GLG	VM2S050C2R1G	VM2S050C2R5G	VM2S050C2S5G
70	S62	3/4	Quad Tri 480	VM1S070C2GLG	VM1S070C2R1G	VM1S070C2R5G	VM2S070C2GLG	VM2S070C2R1G	VM2S070C2R5G	VM2S070C2S5G
				VM1S076C2GLG	VM1S076C2R1G	VM1S076C2R5G	VM2S076C2GLG	VM2S076C2R1G	VM2S076C2R5G	VM2S076C2S5G
				VM1S075C2GLG	VM1S075C2R1G	VM1S075C2R5G	VM2S075C2GLG	VM2S075C2R1G	VM2S075C2R5G	VM2S075C2S5G
100	S54	3/4	Quad Tri 480	VM1S100C2GLG	VM1S100C2R1G	VM1S100C2R5G	VM2S100C2GLG	VM2S100C2R1G	VM2S100C2R5G	VM2S100C2S5G
				VM1S106C2GLG	VM1S106C2R1G	VM1S106C2R5G	VM2S106C2GLG	VM2S106C2R1G	VM2S106C2R5G	VM2S106C2S5G
				VM1S105C2GLG	VM1S105C2R1G	VM1S105C2R5G	VM2S105C2GLG	VM2S105C2R1G	VM2S105C2R5G	VM2S105C2S5G
150	S55	3/4	Quad Tri 480	VM1S150C2GLG	VM1S150C2R1G	VM1S150C2R5G	VM2S150C2GLG	VM2S150C2R1G	VM2S150C2R5G	VM2S150C2S5G
				VM1S156C2GLG	VM1S156C2R1G	VM1S156C2R5G	VM2S156C2GLG	VM2S156C2R1G	VM2S156C2R5G	VM2S156C2S5G
				VM1S155C2GLG	VM1S155C2R1G	VM1S155C2R5G	VM2S155C2GLG	VM2S155C2R1G	VM2S155C2R5G	VM2S155C2S5G

VM 35 - 150 HIGH PRESSURE SODIUM -EZ ADAPTER ②										
DESCRIPTION				5-1/2" OPTIC THREAD SIZE ②			7-3/4" OPTIC THREAD SIZE ②			
WATTS	ANSI	HUB SIZE③	VOLTAGE ④	GLOBE & GUARD	TYPE I GLASS REFRACTOR & GUARD	TYPE V GLASS REFRACTOR & GUARD	GLOBE & GUARD	TYPE I GLASS REFRACTOR & GUARD	TYPE V GLASS REFRACTOR & GUARD	12" SPIN-TOP TYPE V REFRACTOR & GUARD
35	S76	⊙	120V	VM1S031EZGLG	VM1S031EZR1G	VM1S031EZR5G	VM2S031EZGLG	VM2S031EZR1G	VM2S031EZR5G	VM2S031EZR5G
50	S68	⊙	Quad	VM1S050EZGLG	VM1S050EZR1G	VM1S050EZR5G	VM2S050EZGLG	VM2S050EZR1G	VM2S050EZR5G	VM2S050EZR5G
70	S62	⊙	Quad Tri 480	VM1S070EZGLG	VM1S070EZR1G	VM1S070EZR5G	VM2S070EZGLG	VM2S070EZR1G	VM2S070EZR5G	VM2S070EZR5G
				VM1S076EZGLG	VM1S076EZR1G	VM1S076EZR5G	VM2S076EZGLG	VM2S076EZR1G	VM2S076EZR5G	VM2S076EZR5G
				VM1S075EZGLG	VM1S075EZR1G	VM1S075EZR5G	VM2S075EZGLG	VM2S075EZR1G	VM2S075EZR5G	VM2S075EZR5G
100	S54	⊙	Quad Tri 480	VM1S100EZGLG	VM1S100EZR1G	VM1S100EZR5G	VM2S100EZGLG	VM2S100EZR1G	VM2S100EZR5G	VM2S100EZR5G
				VM1S106EZGLG	VM1S106EZR1G	VM1S106EZR5G	VM2S106EZGLG	VM2S106EZR1G	VM2S106EZR5G	VM2S106EZR5G
				VM1S105EZGLG	VM1S105EZR1G	VM1S105EZR5G	VM2S105EZGLG	VM2S105EZR1G	VM2S105EZR5G	VM2S105EZR5G
150	S55	⊙	Quad Tri 480	VM1S150EZGLG	VM1S150EZR1G	VM1S150EZR5G	VM2S150EZGLG	VM2S150EZR1G	VM2S150EZR5G	VM2S150EZR5G
				VM1S156EZGLG	VM1S156EZR1G	VM1S156EZR5G	VM2S156EZGLG	VM2S156EZR1G	VM2S156EZR5G	VM2S156EZR5G
				VM1S155EZGLG	VM1S155EZR1G	VM1S155EZR5G	VM2S155EZGLG	VM2S155EZR1G	VM2S155EZR5G	VM2S155EZR5G

① See hazardous location data pages L131 - L140 for application suitability.

② Catalog numbers shown are with Guard; to omit guard change ending G to N; e.g. VM1S050C2GLN.

③ Catalog numbers shown are with 3/4" conduit openings; change "2" to "3" for 1" e.g. VM1S050C3GLG.

④ Consult catalog logic for other available voltage & lamp combinations.

⑤ Add suffix NR for AEx nR Restricted Breathing; see page L84 for more information (Ⓢ only)

⑥ VMEZA tank adapters UL "classified" as an assembly for use between VM tanks and EZ mounts. Order EZ mounts separately. See page L101.



LIGHTING

CERTILITE® V SERIES

HIGH PRESSURE SODIUM, 35-150W MEDIUM BASE HID



VM1 Stanchion 25°
w/5-1/2"
Globe & Guard



VM2 Stanchion 25°
w/7-3/4"
Globe & Guard



VM1 Stanchion
Straight
w/5-1/2"
Refractor & Guard



VM2 Stanchion
Straight
w/7-3/4"
Refractor & Guard

VM 35 - 150 HIGH PRESSURE SODIUM -STANCHION 25° ANGLE

DESCRIPTION				5-1/2" OPTIC THREAD SIZE②			7-3/4" OPTIC THREAD SIZE②			
WATTS	ANSI	HUB SIZE③	VOLTAGE④	GLOBE & GUARD	TYPE I GLASS REFRACTOR & GUARD	TYPE V GLASS REFRACTOR & GUARD	GLOBE & GUARD	TYPE I GLASS REFRACTOR & GUARD	TYPE V GLASS REFRACTOR & GUARD	12" SPIN-TOP TYPE V REFRACTOR & GUARD
35	S76	1-1/2"	120V	VM1S031D5GLG	VM1S031D5R1G	VM1S031D5R5G	VM2S031D5GLG	VM2S031D5R1G	VM2S031D5R5G	VM2S031D5S5G
50	S68	1-1/2"	Quad	VM1S050D5GLG	VM1S050D5R1G	VM1S050D5R5G	VM2S050D5GLG	VM2S050D5R1G	VM2S050D5R5G	VM2S050D5S5G
70	S62	1-1/2"	Quad Tri 480	VM1S070D5GLG	VM1S070D5R1G	VM1S070D5R5G	VM2S070D5GLG	VM2S070D5R1G	VM2S070D5R5G	VM2S070D5S5G
				VM1S076D5GLG	VM1S076D5R1G	VM1S076D5R5G	VM2S076D5GLG	VM2S076D5R1G	VM2S076D5R5G	VM2S076D5S5G
				VM1S075D5GLG	VM1S075D5R1G	VM1S075D5R5G	VM2S075D5GLG	VM2S075D5R1G	VM2S075D5R5G	VM2S075D5S5G
100	S54	1-1/2"	Quad Tri 480	VM1S100D5GLG	VM1S100D5R1G	VM1S100D5R5G	VM2S100D5GLG	VM2S100D5R1G	VM2S100D5R5G	VM2S100D5S5G
				VM1S106D5GLG	VM1S106D5R1G	VM1S106D5R5G	VM2S106D5GLG	VM2S106D5R1G	VM2S106D5R5G	VM2S106D5S5G
				VM1S105D5GLG	VM1S105D5R1G	VM1S105D5R5G	VM2S105D5GLG	VM2S105D5R1G	VM2S105D5R5G	VM2S105D5S5G
150	S55	1-1/2"	Quad Tri 480	VM1S150D5GLG	VM1S150D5R1G	VM1S150D5R5G	VM2S150D5GLG	VM2S150D5R1G	VM2S150D5R5G	VM2S150D5S5G
				VM1S156D5GLG	VM1S156D5R1G	VM1S156D5R5G	VM2S156D5GLG	VM2S156D5R1G	VM2S156D5R5G	VM2S156D5S5G
				VM1S155D5GLG	VM1S155D5R1G	VM1S155D5R5G	VM2S155D5GLG	VM2S155D5R1G	VM2S155D5R5G	VM2S155D5S5G

VM 35 - 150 HIGH PRESSURE SODIUM -STANCHION STRAIGHT

DESCRIPTION				5-1/2" OPTIC THREAD SIZE②			7-3/4" OPTIC THREAD SIZE②			
WATTS	ANSI	HUB SIZE③	VOLTAGE④	GLOBE & GUARD	TYPE I GLASS REFRACTOR & GUARD	TYPE V GLASS REFRACTOR & GUARD	GLOBE & GUARD	TYPE I GLASS REFRACTOR & GUARD	TYPE V GLASS REFRACTOR & GUARD	12" SPIN-TOP TYPE V REFRACTOR & GUARD
35	S76	1-1/2"	120V	VM1S031S5GLG	VM1S031S5R1G	VM1S031S5R5G	VM2S031S5GLG	VM2S031S5R1G	VM2S031S5R5G	VM2S031S5S5G
50	S68	1-1/2"	Quad	VM1S050S5GLG	VM1S050S5R1G	VM1S050S5R5G	VM2S050S5GLG	VM2S050S5R1G	VM2S050S5R5G	VM2S050S5S5G
70	S62	1-1/2"	Quad Tri 480	VM1S070S5GLG	VM1S070S5R1G	VM1S070S5R5G	VM2S070S5GLG	VM2S070S5R1G	VM2S070S5R5G	VM2S070S5S5G
				VM1S076S5GLG	VM1S076S5R1G	VM1S076S5R5G	VM2S076S5GLG	VM2S076S5R1G	VM2S076S5R5G	VM2S076S5S5G
				VM1S075S5GLG	VM1S075S5R1G	VM1S075S5R5G	VM2S075S5GLG	VM2S075S5R1G	VM2S075S5R5G	VM2S075S5S5G
100	S54	1-1/2"	Quad Tri 480	VM1S100S5GLG	VM1S100S5R1G	VM1S100S5R5G	VM2S100S5GLG	VM2S100S5R1G	VM2S100S5R5G	VM2S100S5S5G
				VM1S106S5GLG	VM1S106S5R1G	VM1S106S5R5G	VM2S106S5GLG	VM2S106S5R1G	VM2S106S5R5G	VM2S106S5S5G
				VM1S105S5GLG	VM1S105S5R1G	VM1S105S5R5G	VM2S105S5GLG	VM2S105S5R1G	VM2S105S5R5G	VM2S105S5S5G
150	S55	1-1/2"	Quad Tri 480	VM1S150S5GLG	VM1S150S5R1G	VM1S150S5R5G	VM2S150S5GLG	VM2S150S5R1G	VM2S150S5R5G	VM2S150S5S5G
				VM1S156S5GLG	VM1S156S5R1G	VM1S156S5R5G	VM2S156S5GLG	VM2S156S5R1G	VM2S156S5R5G	VM2S156S5S5G
				VM1S155S5GLG	VM1S155S5R1G	VM1S155S5R5G	VM2S155S5GLG	VM2S155S5R1G	VM2S155S5R5G	VM2S155S5S5G

① See hazardous location data pages L131 - L140 for application suitability.

② Catalog numbers shown are with Guard; to omit guard change ending G to N; e.g. VM1S050D5GLN.

③ Catalog numbers shown are with 1-1/2" conduit openings; change "5" to "4" for 1-1/4" e.g. VM1S050D4GLG.

④ Consult catalog logic for other available voltage & lamp combinations.

⑤ Add suffix NR for AEx nR Restricted Breathing; see page L84 for more information (Ⓢ only)