

# Eaton NZM2-XR24-30DC

Catalog Number: NZM2-XR24-30DC

Eaton molded case circuit breaker accessory box terminal, Remote operator, 24-30 Vdc, NZM2, Series NZM, 24-30 Vdc

## General specifications



### Product Name

Eaton molded case circuit breaker  
accessory box terminal

### Catalog Number

NZM2-XR24-30DC

### EAN

4015082598365

### Product Length/Depth

1.378 in

### Product Height

1.378 in

### Product Width

1.378 in

### Product Weight

3.995 lb

### Warranty

Eaton Selling Policy 25-000, one (1) year Contact Manufacturer from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

### Compliances

## Product specifications

### Series

Series NZM

### Rated control supply voltage

24-30 Vdc

### Type

Remote operator

### Used with

NZM2

### Voltage rating

24-30 Vdc

## Resources

### Catalogs

[Compact circuit-breakers and switch-disconnectors up to 1600 A](#)

### Multimedia

[Flex shaft handle installation tutorial](#)

### Specifications and datasheets

[Eaton Specification Sheet - NZM2-XR24-30DC](#)

[Product Data Sheet - NZM2-XR24-30DC](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)