

CONDUIT BODIES • COVERS • GASKETS

Malleable Iron Conduit Body Covers



Applications

To cover conduit body opening

Features

- Supplied with stainless steel captive screws
- Sizes 2-1/2" thru 4" with raised dome affords additional wiring room

Standard Materials

Malleable iron

Standard Finish

Zinc plated

Applicable Third Party Standards

- UL Standard: 514A
- Fed. Spec. W-C-586D
- NEMA: FB-1
- UL Listed File # E208392



1/2" through 2"



2 1/2" through 4"

Raised Dome affords additional wiring room

CATALOG NUMBER	TRADE SIZE	DIM A	DIM B	DIM C	MASTER PACK	WEIGHT PER C
CM1KON	1/2"	3.938	1.313	0.188	50	23.4
CM2KON	3/4"	4.625	1.5	0.188	50	30.6
CM3KON	1"	5.313	1.75	0.25	50	40.6
CM4KON	1-1/4 – 1-1/2"	7.188	2.5	0.313	50	91.3
CM5KON	2"	9.5	3.188	0.313	25	208.1
CM6KON	2-1/2" – 3"	12.25	4.313	1.063	10	358.1
CM7KON	3-1/2 – 4"	14.875	5.625	1.125	5	550.0