

PRODUCT INFORMATION PACKET



Model No: C4D17WK3G

Catalog No: 108232.00

1.5HP.1750RPM.S56C.TEFC.180V.CONT.40C.1.0SF.RIGID C.WASHGUARD.C4D17WK3G
White Epoxy



Regal and Leeson are trademarks of Regal Beloit Corporation or one of its affiliated companies.

©2018 Regal Beloit Corporation, All Rights Reserved. MC017097E





Nameplate Specifications

Output HP	1.50 Hp	Output KW	1.1 kW
Voltage	180 V	Current	7.6 A
Speed	1750 rpm	Service Factor	1
Efficiency	86.5 %	Duty	Continuous
Insulation Class	H	Frame	S56C
Enclosure	Totally Enclosed Fan Cooled	Overload Protector	No
Ambient Temperature	40 °C	Drive End Bearing Size	6203
Opp Drive End Bearing Size	6203	UL	Recognized
CSA	Y	CE	N

Technical Specifications

Rotation	Reversible	Mounting	Rigid C base
Overall Length	16.82 in	Frame Length	9.47 in
Shaft Diameter	0.625 in	Shaft Extension	2.06 in
Outline Drawing	031909-108232		

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created: 10/15/2018

