

PRODUCT INFORMATION PACKET



Model No: C4D28FK11G

Catalog No: 108265.00

..1 1/2HP..2500RPM.S56C.TEFC.180V...CONT.40C.1.0SF.RIGID C.C4D28FK11.....DC NEMA.....
SCR



Regal and Leeson are trademarks of Regal Beloit Corporation or one of its affiliated companies.

©2018 Regal Beloit Corporation, All Rights Reserved. MC017097E





Nameplate Specifications

Output HP	1.50 Hp	Output KW	1.1 kW
Voltage	180 V	Current	7.5 A
Speed	2500 rpm	Service Factor	1
Efficiency	85.3 %	Duty	Continuous
Insulation Class	H	Frame	S56C
Enclosure	Totally Enclosed Fan Cooled	Overload Protector	No
Ambient Temperature	40 °C	Drive End Bearing Size	6203
Opp Drive End Bearing Size	6203	UL	Recognized
CSA	Y	CE	N

Technical Specifications

Rotation	Reversible	Mounting	Rigid C base
Overall Length	15.32 in	Frame Length	7.97 in
Shaft Diameter	0.625 in	Shaft Extension	2.06 in
Outline Drawing	031879-108265		

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created: 10/15/2018

