

# PRODUCT INFORMATION PACKET



Model No: C4D28FK12E

Catalog No: 108266.00

2HP.2500RPM.S56CZ.TEFC.180V.CONT.40C.1.0SF.RIGID C.DC NEMA.C4D28FK12E  
SCR



Regal and Leeson are trademarks of Regal Beloit Corporation or one of its affiliated companies.

©2018 Regal Beloit Corporation, All Rights Reserved. MC017097E





### Nameplate Specifications

Output HP	2 Hp	Output KW	1.5 kW
Voltage	180 V	Current	8.6 A
Speed	2500 rpm	Service Factor	1
Efficiency	88.1 %	Duty	Continuous
Insulation Class	F	Frame	S56CZ
Enclosure	Totally Enclosed Fan Cooled	Overload Protector	No
Ambient Temperature	40 °C	Drive End Bearing Size	6205
Opp Drive End Bearing Size	6203	UL	Recognized
CSA	Y	CE	N

### Technical Specifications

Rotation	Reversible	Mounting	Rigid C base
Overall Length	17.89 in	Frame Length	10.47 in
Shaft Diameter	0.875 in	Shaft Extension	2.13 in
Outline Drawing	031897-108266		

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created: 10/15/2018

