

# PRODUCT INFORMATION PACKET



Model No: CI4D34FT2C

Catalog No: 108373.00

..1.1KW-1 1/2HP..3000RPM.80.IP54.180V...S1.40C.1,0SF.SPECIAL.CI4D34FT2C.....DC METRIC.....

Metric Motors



Regal and Leeson are trademarks of Regal Beloit Corporation or one of its affiliated companies.

©2018 Regal Beloit Corporation, All Rights Reserved. MC017097E





### Nameplate Specifications

Output KW	1.5 kW	Voltage	180 V
Current	9.3 A	Speed	3000 rpm
Service Factor	1	Efficiency	87 %
Duty	S1	Insulation Class	F
Frame	80	Enclosure	IP54
Overload Protector	No	Ambient Temperature	40 °C
Drive End Bearing Size	6204	Opp Drive End Bearing Size	6203
UL	Recognized	CSA	Y
CE	Y		

### Technical Specifications

Rotation	Reversible	Mounting	Special
Overall Length	15.15 in	Frame Length	7.47 in
Shaft Diameter	0.750 in	Shaft Extension	2.05 in
Outline Drawing	031898-108373		

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created: 10/15/2018

