

PRODUCT INFORMATION PACKET



Model No: C4D18FK1D

Catalog No: 109101.00

..1HP..1800RPM.S56C.TEFC.36V...CONT.40C.1.0SF.RIGID C.C4D18FK1.....DC NEMA LOW VOLTAGE.....

Low Voltage



Regal and Leeson are trademarks of Regal Beloit Corporation or one of its affiliated companies.

©2018 Regal Beloit Corporation, All Rights Reserved. MC017097E





Nameplate Specifications

Output HP	1 Hp	Output KW	0.75 kW
Voltage	36 V	Current	25.5 A
Speed	1800 rpm	Service Factor	1
Efficiency	82.8 %	Duty	Continuous
Insulation Class	H	Frame	S56C
Enclosure	Totally Enclosed Fan Cooled	Overload Protector	No
Ambient Temperature	40 °C	Drive End Bearing Size	6203
Opp Drive End Bearing Size	6203	UL	Recognized
CSA	Y	CE	N

Technical Specifications

Rotation	Reversible	Mounting	Rigid C base
Overall Length	13.82 in	Frame Length	6.47 in
Shaft Diameter	0.625 in	Shaft Extension	2.06 in
Outline Drawing	031891-109101		

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created: 10/15/2018

