

PRODUCT INFORMATION PACKET



Model No: C4D18VK7A

Catalog No: 109296.00

1/4HP.1800RPM.S56C.TENV.12V.CONT.40C.1.0SF.RIGID C.DC NEMA LOW VOLTAGE.C4D18VK7
WASHDOWN DUTY

Low Voltage



Regal and Leeson are trademarks of Regal Beloit Corporation or one of its affiliated companies.

©2018 Regal Beloit Corporation, All Rights Reserved. MC017097E

REGAL




Nameplate Specifications

Output HP	0.25 Hp	Output KW	0.19 kW
Voltage	12 V	Current	21.0 A
Speed	1800 rpm	Service Factor	1
Efficiency	72.1 %	Duty	Continuous
Insulation Class	F	Frame	S56C
Enclosure	Totally Enclosed Non Ventilated	Overload Protector	No
Ambient Temperature	40 °C	Drive End Bearing Size	6203
Opp Drive End Bearing Size	6203	UL	Recognized
CSA	Y	CE	N

Technical Specifications

Rotation	Reversible	Mounting	Rigid C base
Overall Length	10.27 in	Frame Length	3.97 in
Shaft Diameter	0.625 in	Shaft Extension	2.06 in
Outline Drawing	612-0209-109296		

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created: 10/15/2018

3 of 3