

PRODUCT INFORMATION PACKET



Model No: C4D18WK12C

Catalog No: 109302.00

1HP.1800RPM.S56C.TEFC.12VDC.CONT.40C.1.0SF.RIGID C.DC NEMA LOW VOLTAGE.C4D18WK12
WASHDOWN DUTY

Low Voltage



Regal and Leeson are trademarks of Regal Beloit Corporation or one of its affiliated companies.

©2018 Regal Beloit Corporation, All Rights Reserved. MC017097E





Nameplate Specifications

Output HP	1 Hp	Output KW	0.75 kW
Voltage	12 V	Current	80.0 A
Speed	1800 rpm	Service Factor	1
Efficiency	77.9 %	Duty	Continuous
Insulation Class	H	Frame	S56C
Enclosure	Totally Enclosed Fan Cooled	Overload Protector	No
Ambient Temperature	40 °C	Drive End Bearing Size	6203
Opp Drive End Bearing Size	6203	UL	Recognized
CSA	Y	CE	N

Technical Specifications

Rotation	Reversible	Mounting	Rigid C base
Overall Length	13.81 in	Frame Length	8.50 in
Shaft Diameter	0.625 in	Shaft Extension	2.06 in
Outline Drawing	612-0217-000		

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created: 10/15/2018