

PRODUCT INFORMATION PACKET



Model No: C6D17EK7A

Catalog No: 118055.00

118055.00..1/3HP..1750RPM.56C.TENV.24VDC.DC.DC.CONT.40C.1.0SF.RIGID C
FACE.C6D17EK7.....LOW VOLTAGE DC EX-PROOF.NONE.....

Explosion Proof



Regal and Leeson are trademarks of Regal Beloit Corporation or one of its affiliated companies.

©2018 Regal Beloit Corporation, All Rights Reserved. MC017097E



**Product Information Packet: Model No: C6D17EK7A, Catalog No:118055.00
118055.00..1/3HP..1750RPM.56C.TENV.24VDC.DC.DC.CONT.40C.1.0SF.RIGID C FACE.C6D17EK7.....LOW
VOLTAGE DC EX-PROOF.NONE.....**



Nameplate Specifications




Output HP	0.33 Hp	Output KW	0.25 kW
Voltage	24 V	Current	13.4 A
Speed	1750 rpm	Service Factor	1
Duty	Continuous	Insulation Class	H
Frame	S56C	Enclosure	Totally Enclosed Non Ventilated
Overload Protector	No	Ambient Temperature	40 °C
UL	Recognized	CSA	Y
CE	N		

Technical Specifications

Rotation	Reversible	Mounting	Rigid C base
Overall Length	12.37 in	Shaft Diameter	0.625 in
Shaft Extension	2.06 in		
Outline Drawing	612-0196-000		

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created: 10/15/2018

612-0196



NOTES:

- 1) ALL DIMENSIONS REFERENCE UNLESS TOLERANCED.
2) UL LISTED (E56538) AND CSA CERTIFIED (LR43478).

VOLTAGE	24 VDC
HORSEPOWER	1/3
RPM	1750
AMPERES	13.4
CONTINUOUS DUTY	
PERMANENT MAGNET FIELD	
CLASS H INSULATION	
BALL BEARINGS	

ITEM No.	ITEM REV
—000	0

		TOLERANCES UNLESS SPECIFIED					ELECTRIC MOTORS GEARMOTORS AND DRIVES	DRAWN IPG 10/22/15
		DEC.	INCHES					
		.X	±.1			TITLE	OUTLINE EXPLOSION PROOF DC MOTOR	CHK
		.XX	±.03					APPD
		.XXX	±.005			MATERIAL	FINISH	SCALE 3=8
		.XXXX	±.0005					REF 034446, 612-0195
A	RELEASED, ECO-0086286	IPG 10/22/15				CAD FILE	612-0196	FMF 118055.00
NO.	REVISION	BY & DATE	CHK	ANG	±1/2"			PREV
THIS DRAWING IN DESIGN AND DETAIL IS OUR PROPERTY AND MUST NOT BE USED EXCEPT IN CONNECTION WITH OUR WORK. ALL RIGHTS OF DESIGN AND INVENTION ARE RESERVED. THIS IS AN ELECTRONICALLY GENERATED DOCUMENT — DO NOT SCALE THIS PRINT						RFP		
						DIST		
							SIZE B	DRAWING NO. 612-0196
								REV. A