

PRODUCT INFORMATION PACKET



Model No: 191545.00
Catalog No: 191545.00
0.33 HP Washdown Motor, 1 phase, 1800 RPM, 115/230 V, 48YZ Frame, TEAO
Washdown Pedestal Fan Motors



Regal and Leeson are trademarks of Regal Beloit Corporation or one of its affiliated companies.
©2019 Regal Beloit Corporation, All Rights Reserved. MC017097E

REGAL




Nameplate Specifications

Output HP	0.33 Hp	Output KW	0.25 kW
Frequency	60 Hz	Voltage	115/230 V
Current	3.0/1.5 A	Speed	1755 rpm
Service Factor	1	Phase	1
Efficiency	74 %	Power Factor	98
Duty	Continuous	Insulation Class	F
Design Code	No Design Code	KVA Code	D
Frame	48YZ	Enclosure	Totally Enclosed Air Over
Thermal Protection	Automatic	Ambient Temperature	40 °C
Drive End Bearing Size	6203	Opp Drive End Bearing Size	6203
UL	Recognized	CSA	Y
CE	N	IP Code	55

Technical Specifications

Electrical Type	Permanent Split Capacitor	Starting Method	Across The Line
Poles	4	Rotation	Selective Clockwise
Resistance Main	14.23 Ohms	Mounting	Round - Extended Studs
Motor Orientation	Horizontal	Drive End Bearing	Ball
Opp Drive End Bearing	Ball	Frame Material	Stainless Steel
Shaft Type	Single Special Extension	Overall Length	11.58 in
Shaft Diameter	0.500 in	Shaft Extension	4.05 in
Assembly/Box Mounting	F1 Only		

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:04/11/2019



DR BY:			
APPD:			
FIRST ANGLE PROJECTION		EDS DATE	
CONFIDENTIAL: THIS DRAWING AND ITS INFORMATION ARE THE EXCLUSIVE AND CONFIDENTIAL PROPERTY OF AN AFFILIATE OF REGAL BELLOUT CORPORATION AND ARE NOT TO BE DISCLOSED, DUPLICATED, DISTRIBUTED OR OTHERWISE USED WITHOUT THE WRITTEN CONSENT OF THE AFFILIATE OF REGAL BELLOUT CORPORATION. ALL RIGHTS RESERVED.			
DESCRIPTION			
Single Phase 48 Stainless Steel Motors			
SIZE		DWG NO	
A3		0119154500	
SCALE		SHEET	
1:1.5			