



Part no.: 50108446
KB SSI/IBS-30000-BA
Interconnection cable



Figure can vary

Contents

- Technical data
- Electrical connection
- Accessories

Technical data

Basic data

Suitable for interface	SSI Interbus-S
------------------------	-------------------

Connection

Connection 1

Type of connection	Connector
Thread size	M12
Type	Female
No. of pins	5 -pin
Encoding	B-coded
Design	Axial

Connection 2

Type of connection	Open end
--------------------	----------

Cable properties

Number of conductors	5 Piece(s)
Sheathing color	Violet
Shielded	Yes
Cable design	Connection cable (open on one end)
Cable diameter (external)	7.5 mm
Cable length	30,000 mm
Sheathing material	PUR

Mechanical data

Classification

eCl@ss 8.0	27279218
eCl@ss 9.0	27060311
ETIM 5.0	EC001855

Electrical connection


Connection 1	
Type of connection	Connector
Thread size	M12
Type	Female
No. of pins	5 -pin
Encoding	B-coded
Design	Axial

Connection 2	
Type of connection	Open end

Part no.: 50108446 – KB SSI/IBS-30000-BA – Interconnection cable

Accessories

General

	Part no.	Designation	Article	Description
	50132266	TT-Set 0,6-13	Tool	Type: Torque key Width across flats: 13 mm Torque: 0.6 N·m Material: Plastic, Stainless steel Ambient temperature: -40 ... 120 °C