



Part no.: 50116939
TK 10.P
Reflector



Figure can vary

Contents

- Technical data
- Dimensioned drawings



Part no.: 50116939 – TK 10.P – Reflector

Technical data

<i>Basic data</i>	
Area of application	Pharmaceutical

<i>Mechanical data</i>	
Design	Round
Mounting dimension, thickness	4 mm
Triple reflector size	1.5 mm
Mounting dimension, diameter	10 mm
Reflection surface diameter	8.5 mm
Reflector material	Plastic
Material of base material	Plastic
Chemical designation, reflector material	PES
Structure, active surface	Triple
Net weight	1 g
Type of fastening	Adhesive
Type of reflector	Reflector
Compatibility of materials	ECOLAB

<i>Environmental data</i>	
Ambient temperature, operation	-40 ... 70 °C

<i>Certifications</i>	
Degree of protection	IP 67

<i>Classification</i>	
eCl@ss 8.0	27279203
eCl@ss 9.0	27273601
ETIM 5.0	EC002467

Dimensioned drawings

All dimensions in millimeters

