



**Part no.: 50112142**  
**TK BR 53**  
**Reflector**



Figure can vary

## Contents

- Technical data
- Dimensioned drawings



Part no.: 50112142 – TK BR 53 – Reflector

## Technical data

<i>Basic data</i>	
Area of application	Food
<i>Mechanical data</i>	
Design	Rectangular
Mounting dimension, width	14 mm
Reflection surface width	29 mm
Mounting dimension, height	36 mm
Reflection surface height	10 mm
Mounting dimension, thickness	20.3 mm
Reflector material	Plastic
Material of base material	Stainless steel
Chemical designation, reflector material	Stainless steel
Structure, active surface	Mikrotriple
Net weight	50 g
Type of fastening	Housing fit
<i>Environmental data</i>	
Ambient temperature, operation	-30 ... 70 °C
<i>Certifications</i>	
Degree of protection	IP 67 IP 69K
<i>Classification</i>	
eCl@ss 8.0	27279203
eCl@ss 9.0	27273601
ETIM 5.0	EC002467

## Dimensioned drawings

All dimensions in millimeters

Part no.: 50112142 – TK BR 53 – Reflector

