

Technical data sheet

Reflector

Part no.: 50022816

TKS 100X100

Contents

- Technical data
- Dimensioned drawings



Figure can vary

Technical data

Mechanical data

Design	Rectangular
Mounting dimension, width	103 mm
Reflection surface width	96 mm
Mounting dimension, height	125 mm
Reflection surface height	96 mm
Mounting dimension, thickness	8.7 mm
Triple reflector size	4 mm
Reflector material	Plastic
Material of base material	Plastic
Chemical designation, reflector material	PMMA8N
Structure, active surface	Triple
Net weight	70 g
Type of fastening	Adhesive Through-hole mounting

Certifications

Degree of protection	IP 67
----------------------	-------

Classification

Customs tariff number	90029000
eCl@ss 5.1.4	27279203
eCl@ss 8.0	27279203
eCl@ss 9.0	27273601
eCl@ss 10.0	27273601
eCl@ss 11.0	27273601
ETIM 5.0	EC002467
ETIM 6.0	EC002467
ETIM 7.0	EC002467

Environmental data

Ambient temperature, operation	-40 ... 65 °C
--------------------------------	---------------

Dimensioned drawings

All dimensions in millimeters

