



**Part no.: 50106958**  
**TKS 20.P**  
**Reflector**



Figure can vary

# Contents

- Technical data



Part no.: 50106958 – TKS 20.P – Reflector

## Technical data

<b>Basic data</b>	
Area of application	Pharmaceutical

  

<b>Mechanical data</b>	
Design	Round
Mounting dimension, thickness	6.5 mm
Triple reflector size	2.3 mm
Mounting dimension, diameter	20 mm
Reflection surface diameter	17 mm
Reflector material	Plastic
Material of base material	Plastic
Chemical designation, reflector material	PES
Structure, active surface	Triple
Net weight	3 g
Type of fastening	M4 threaded pin
Type of reflector	Reflector
Compatibility of materials	ECOLAB

  

<b>Environmental data</b>	
Ambient temperature, operation	-40 ... 70 °C

  

<b>Certifications</b>	
Degree of protection	IP 67

  

<b>Classification</b>	
eCl@ss 8.0	27279203
eCl@ss 9.0	27273601
ETIM 5.0	EC002467