

Single Phase ODP Motors

Capacitor Start – General Purpose

Single Phase – Drip-Proof – Rigid Base

HP	SYN RPM 60 Hz	NEMA Frame	▼ Catalog Number	Stock	Model Number	App. Wgt. (lbs)	Voltage	Over-load Prot.	F. L. Amps @ 230 V	Service Factor	"C" Dim. (Inches)	♥Notes	
1	3600	56	110360.00	✓	C6C34DB19	28	115/208-230	None	6.0	1.25	10.84	S, US	
			110097.00	✓	M6C34DB3	28	115/208-230	Man.	6.0	1.25	10.84	S, US	
	1800	56	110004.00	✓	C6C17DB2	28	115/208-230	None	6.4	1.15	10.88	S, US	
			LM24580	✓	SRD4SITIC6028TP1	20	115/208-230	None	6.7	1.15	11.44	S, MX	
			110167.00	✓	M6C17DB7	30	115/208-230	Man.	6.4	1.15	10.88	S, US	
			LM24582	✓	SRD4S1T1C6028TP1	29	115/208-230	Man.	6.7	1.15	11.44	S, MX	
			113630.00	✓	M6K17DB33	31	115/208-230	Man.	5.3	1.15	10.88	S, US, 53	
			110000.00	✓	A6C17DB1	28	115/208-230	Auto.	6.4	1.15	10.88	S, US	
			143T	120044.00	✓	C143C17DB3	38	115/208-230	None	6.4	1.15	11.13	S, US
			143T	120003.00	✓	M143C17DB2	33	115/208-230	Man.	6.4	1.15	11.13	S, US
143T	120000.00	✓	A143C17DB1	32	115/208-230	Auto.	6.4	1.15	11.13	S, US			
1 1/2	3600	56	110361.00	✓	C6C34DB20	29	115/208-230	None	8.2	1.15	10.84	S, US	
			110110.00	✓	M6C34DB4	28	115/208-230	Man.	8.2	1.15	10.84	S, US	
	3600	56	113631.00	✓	M6K34DB15	36	115/208-230	Man.	6.2	1.15	11.34	S, US, 53	
			143T	120107.00	C/A	C143C34DB1	32	115/208-230	None	8.2	1.15	11.28	S, US
			56H	110005.00	✓	C6K17DB1	37	115/208-230	None	8.6	1.15	11.84	S, US, 53
			56H	LM24583	C/A	SRD4S1.5T1C6028	40	115/208-230	None	9.0	1.15	12.44	S, MX
			56H	110006.00	✓	P6K17DB2	38	115/208-230	Man.	8.6	1.15	11.84	S, US, 53
			56H	113266.00	✓	M6K17DB30	42	115/208-230	Man.	6.7	1.15	12.38	S, US, 53
			145T	120042.00	✓	C145K17DB5	38	115/208-230	None	8.6	1.15	12.28	S, US, 53
			145T	LM24687	✓	SSD4S1.5T1C6028	41	115/208-230	None	9.0	1.15	12.44	S, MX
1800	145T	120004.00	✓	P145K17DB3	40	115/208-230	Man.	8.6	1.15	12.28	S, US, 53		
		120001.00	✓	U145K17DB1	40	115/208-230	Auto.	8.6	1.15	12.28	S, US, 53		
2	3600	56	110363.00	✓	C6C34DB22	37	115/208-230	None	10.0	1.15	11.84	S, US	
			110362.00	C/A	P6C34DB21	38	115/208-230	Man.	10.0	1.15	12.34	S, US	
	3600	56	113632.00	✓	P6K34DB16	38	115/208-230	Man.	8.6	1.15	11.34	S, US, 53	
			145T	120106.00	✓	C145C34DB3	40	115/208-230	None	10.0	1.15	12.28	S, US
			56H	116704.00	✓	P6K17DB47	45	115/208-203	Man.	8.6	1.15	12.88	S, US, 53
			145T	120067.00	✓	C145K17DB9	42	115/230	None	10.5	1.15	13.28	S, US, 53
			145T	LM24677	✓	SSD4S2T1B6028	49	115/208-230	None	10.5	1.15	13.49	S, MX, 53
			145T	120879.00	✓	P145K17DB38	51	115/208-230	Man.	8.6	1.15	13.31	S, US, 53
			182T	131515.00	✓	C182C17DB8	56	115/208-230	None	12.4	1.15	13.19	S, MX
			182T	131536.00	✓	P182C17DB10	63	115/208-230	Man.	12.4	1.15	13.19	S, MX
182T	131535.00	✓	U182C17DB9	63	115/208-230	Auto.	12.4	1.15	13.19	S, MX			

▼ LM Numbers are Lincoln Models

C/A - Check Availability

Specifications are subject to change without notice

♥ Note listing on inside back flap

Continued On Next Page



Tech Information

Single Phase ODP Motors

Single Phase TEFC Motors

Single Phase C Face Motors

Three Phase ODP Motors

Three Phase TEFC Motors

Three Phase C Face Motors

Inverter Duty Motors

Severe Duty Motors