

# Single Phase TEFC Motors

## Capacitor Start – General Purpose

### Single Phase - TEFC - Rigid Base

HP	SYN RPM 60 Hz	NEMA Frame	▼ Catalog Number	Stock	Model Number	App. Wgt. (lbs)	Voltage	Over-load Prot.	F. L. Amps @ 230 V	Service Factor	"C" Dim. (Inches)	♥ Notes	
2	3600	56H	110352.00	✓	C6C34FB21	41	115/208-230	None	10.0	1.00	13.31	S, US	
			110402.00	✓	P6C34FB23	41	115/208-230	Man.	10.0	1.00	13.31	S, US	
		LM24534	C/A	SRF2S2T1B6028TP1	40	115/208-230	Man.	9.0	1.15	13.32	S, MX, 53		
		145T	120036.00	✓	C145C34FB1	42	115/208-230	None	10.0	1.00	13.75	S, US	
		145T	LM24712	C/A	SRF2ST1B6028	54	115/208-230	None	9.0	1.15	13.37	S, MX, 53	
		145T	120395.00	✓	P145C34FB5	44	115/208-230	Man.	10.0	1.00	13.75	S, US	
	1800	56HZ	113770.00	✓	M6K17FB38	49	230	Man.	8.2	1.15	14.25	S, US, 3, 53	
		145T	121507.00	✓	C145K17FB24	48	115/208-230	None	9.2	1.15	13.75	S, US, 53	
		145T	120867.00	✓	P145K17FB22	48	115/208-230	Man.	9.2	1.00	13.75	S, US, 53	
		182T	131509.00	✓	C182C17FB11	65	115/208-230	None	12.4	1.00	14.46	S, MX	
		182T	LM24713	✓	SS18F4S21B028	54	115/208-230	None	12.4	1.15	14.46	S, MX, 53	
		215T	140747.00	C/A	C215K11FB3	118	115/208-230	None	11.2	1.15	18.71	S, MX, 53	
3	3600	56H	116705.00	✓	P6K34FB31	53	208-230	Man.	14.0	1.00	13.81	S, US, 53	
			145T	120341.00	✓	C145K34FB3	46	230	None	13.0	1.00	14.25	S, US, 53
		145T	LM24714	✓	SS14F2S3T1B6008	48	208-230	None	11.8	1.15	14.87	S, MX, 53	
		182T	131637.00	✓	C182K34FB2	78	115/208-230	None	13.4	1.15	14.96	S, MX, 53	
	1800	184T	131533.00	✓	C184C17FB12	83	115/230	None	16.8	1.00	16.46	S, MX	
		184T	LM24716	C/A	SS184F4S3T1C6028	99	115/208-230	None	16.8	1.00	16.46	S, MX	
		184T	131855.00	✓	P184K17FB26	88	230	Man.	13.6	1.15	14.96	S, MX, 53	
		184T	131549.00	✓	C184K34FB6	93	230	None	19.8	1.15	16.96	S, MX, 53	
5	3600	184T	132042.00	✓	P184K34FB9	103	230	Man.	19.8	1.15	16.97	S, MX, 53	
			131538.00	✓	C184K17FB15	95	230	None	23.0	1.00	17.46	S, MX, 53	
	1800	184T	LM24718	✓	SSF4S5T1B6008	98	208-230	None	21.7	1.00	17.46	S, MX, 53	
			131856.00	✓	P184K17FB25	95	230	Man.	21.0	1.00	15.96	S, MX, 53	
	7 1/2	3600	213T	140684.00	✓	C213K34FB1	120	208-230	None	32.0	1.00	18.34	S, MX, 53
				LM24719	✓	DDF2S7.51B6008	120	208-230	None	32.0	1.00	18.73	S, MX, 53
1800		215T	140120.00	✓	N215K17FB1	169	230	None	33.6	1.15	20.21	S, MX, 53	
			LM24720	✓	SS215F4S7.5T1B6008	133	208-230	None	30.0	1.00	21.09	S, MX, 53	
10	3600	215T	140685.00	✓	C215K34FB1	138	208-230	None	41.5	1.00	19.84	S, MX, 53	
			LM24721	✓	SSF2S10T1B6008	138	208-230	None	41.5	1.00	20.23	S, MX, 53	
	1800	215T	140581.00	✓	C215K17FB12	202	230	None	40.0	1.15	20.71	S, MX, 53	
			LM24722	✓	SSF4S10T1B66	155	230	None	41.5	1.00	21.09	S, MX, 53	

Green items are Premium Efficient

♥ Note listing on inside back flap

▼ LM Numbers are Lincoln Models

C/A - Check Availability

Specifications are subject to change without notice



Tech Information

Single Phase ODP Motors

Single Phase TEFC Motors

Single Phase C Face Motors

Three Phase ODP Motors

Three Phase TEFC Motors

Three Phase C Face Motors

Inverter Duty Motors

Severe Duty Motors