

Single Phase - C Face Motors

Drip-Proof - Capacitor Start

General Purpose - C Face Less Base

Single Phase - Drip-Proof - C Face Less Base

HP	SYN RPM 60 Hz	NEMA Frame	▼ Catalog Number	Stock	
1/4	1800	S56C	100023.00	✓	
	1800	S56C	101521.00	✓	
1/3	3600	S56C	100354.00	✓	
	3600	S56C	100355.00	✓	
1800	S56C	100024.00	✓		
	S56C	LM24571	✓		
	S56C	100018.00	✓		
	S56C	101522.00	✓		
	S56C	100356.00	✓		
1/2	3600	S56C	100054.00	✓	
	3600	S56C	100025.00	✓	
1800	S56C	100019.00	✓		
	S56C	100020.00	✓		
	56C	110381.00	✓		
	3/4	3600	S56C	100357.00	✓
		3600	S56C	100055.00	✓
1800	S56C	100026.00	✓		
	S56C	LM24505	✓		
	S56C	100021.00	✓		
	S56C	101523.00	✓		
	1200	56C	110382.00	✓	
1	3600	56C	110384.00	✓	
	3600	56C	113337.00	C/A	
1800	56C	110220.00	✓		
	56C	110036.00	✓		
	143TC	121002.00	✓		

Model Number	App. Wgt. (lbs)	Voltage	Over-load Prot.	F. L. Amps @ 230 V	Service Factor	"C" Dim. (Inches)	♥ Notes
C4C17DC7	17	115/208-230	None	2.7	1.35	9.24	S, MX
A4C17DC79	17	115/208-230	Auto.	2.7	1.35	9.24	S, MX
C4C34DC11	17	115/208-230	None	2.8	1.35	8.99	S, MX
A4C34DC12	17	115/208-230	Auto.	2.8	1.35	8.99	S, MX
C4C17DC8	17	115/208-230	None	3.3	1.35	9.24	S, MX
SRD4S0.33TLCN1C6028	17	115/208-230	None	3.2	1.35	10.69	S, MX
M4C17DC2	18	115/208-230	Man.	3.3	1.35	9.24	S, MX
A4C17DC81	17	115/208-230	Auto.	3.3	1.35	9.24	S, MX
C4C34DC13	19	115/208-230	None	3.4	1.25	9.99	S, MX
A4C34DC1	18	115/208-230	Auto.	3.4	1.25	9.99	S, MX
C4C17DC9	19	115/208-230	None	4.4	1.25	9.99	S, MX
M4C17DC3	21	115/208-230	Man.	4.4	1.25	9.99	S, MX
A4C17DC4	20	115/208-230	Auto.	4.4	1.25	9.99	S, MX
C6C11DC2	32	115/208-230	None	5.0	1.25	11.38	S, US
C4C34DC14	24	115/208-230	None	4.9	1.25	10.49	S, MX
A4C34DC2	24	115/208-230	Auto.	4.9	1.25	10.49	S, MX
C4C17DC10	24	115/208-230	None	5.4	1.25	10.99	S, MX
SRD4S0.75TLCN1B6028	25	115/208-230	None	5.5	1.25	11.72	S, MX, 53
M4C17DC5	24	115/208-230	Man.	5.4	1.25	10.99	S, MX
A4C17DC80	26	115/208-230	Auto.	5.4	1.25	10.99	S, MX
C6C11DC3	46	115/208-230	None	6.4	1.15	12.88	S, US
C6C34DC24	28	115/208-230	None	6.0	1.25	10.88	S, US
A6C34DC53	28	115/208-230	Auto.	6.0	1.25	10.84	S, US
C6C17DC3	30	115/208-230	None	6.4	1.15	10.88	S, US
M6C17DC1	27	115/208-230	Man.	6.4	1.15	10.88	S, US
C143C17DC2	31	115/208-230	None	6.4	1.15	11.28	S, US

▼ LM Numbers are Lincoln Models

C/A - Check Availability

Specifications are subject to change without notice

♥ Note listing on inside back flap

Continued On Next Page

Tech Information

Single Phase
ODP Motors

Single Phase
TEFC Motors

Single Phase
C Face Motors

Three Phase
ODP Motors

Three Phase
TEFC Motors

Three Phase
C Face Motors

Inverter Duty
Motors

Severe Duty
Motors

