

Single Phase - C Face Motors

Totally Enclosed - Capacitor Start - General Purpose

Single Phase - Totally Enclosed - C Face Less Base

HP	SYN RPM 60 Hz	NEMA Frame	▼ Catalog Number	Stock	Model Number	App. Wgt. (lbs)	Voltage	Over-load Prot.	F. L. Amps @ 230 V	Service Factor	"C" Dim. (Inches)	♥Notes
1/6	1800	48CZ	102661.00	✓	C4C17FC25	14	115/208-230	None	2.0	1.15	9.19	S, MX, 25
1/4	1800	48CZ	101765.00	✓	C4C17FC10	18	115/208-230	None	2.7	1.15	9.19	S, MX, 25
		S56C	102868.00	✓	C4C17NC26	22	115/208-230	None	2.3	1.15	9.80	S, MX, 12
		S56C	LM24733	✓	SRN4S0.25TLCN1C6028	18	115/208-230	None	2.1	1.00	9.94	S, MX
		S56C	102866.00	✓	C4C17FC34	18	115/208-230	None	2.7	1.15	9.44	S, MX
1/3	3600	S56C	102870.00	✓	C4C34FC13	20	115/208-230	None	2.8	1.15	9.44	S, MX
		S56C	102873.00	✓	C4C34NC15	24	115/208-230	None	1.9	1.00	9.30	S, MX
		S56C	LM24734	✓	SRN2S0.33TLCN1C6028	20	115/208-230	None	2.2	1.15	10.19	S, MX
		48CZ	102663.00	✓	C4C17FC26	19	115/208-230	None	3.3	1.15	9.69	S, MX, 25
1800	S56C	101766.00	✓	C4C17FC9	22	115/208-230	None	3.3	1.15	9.94	S, MX	
		102867.00	✓	C4C17NC25	23	115/208-230	None	2.6	1.15	10.30	S, MX, 12	
		LM24598	✓	SRF4S0.33TLCN1C6028	19	115/208-230	None	3.9	1.15	12.32	S, MX	
		102869.00	✓	M4C17NC27	25	115/208-230	Man.	2.6	1.15	10.30	S, MX, 12	
1200	56C	LM24735	C/A	SRF6S0.33TLCN1C6028	28	115/208-230	None	3.9	1.15	12.32	S, MX	
1/2	3600	S56C	102864.00	✓	C4C34FC12	22	115/208-230	None	3.5	1.15	9.94	S, MX
		56C	LM24736	✓	SRF2S0.5TLCN1C6028	23	115/208-230	None	4.2	1.15	11.82	S, MX
		S56C	102872.00	✓	M4C34FC14	25	115/208-230	Man.	3.5	1.15	9.94	S, MX
		48CZ	102665.00	C/A	C4C17FC27	22	115/208-230	None	4.0	1.00	10.44	S, MX, 25
1800	S56C	102862.00	✓	C4C17FC32	21	115/208-230	None	4.0	1.15	10.69	S, MX	
		56C	LM24599	✓	SRF4S0.5TLCN1C6028	24	115/208-230	None	4.4	1.15	11.19	S, MX
		S56C	102865.00	✓	M4C17FC33	22	115/208-230	Man.	4.0	1.15	10.69	S, MX
		S56C	102871.00	✓	A4C17FC35	24	115/208-230	Auto.	4.0	1.15	10.69	S, MX
1200	56C	110411.00	✓	C6C11FC1	37	115/208-230	None	4.9	1.00	12.81	S, US	
3/4	3600	56C	110413.00	✓	C6C34FC8	26	115/208-230	None	5.0	1.15	11.31	S, US
		56C	LM24738	✓	SRF2S0.75TLCN1C5028	30	115/208-230	None	5.3	1.15	12.32	S, MX
		56C	110412.00	✓	M6C34FC7	28	115/208-230	Man.	5.0	1.15	11.31	S, US
		56C	110057.00	✓	C6C17FC6	25	115/208-230	None	5.4	1.15	11.31	S, US
1800	S56C	LM24613	✓	SRF4S0.75TLCN1C6028	30	115/208-230	None	5.5	1.15	12.32	S, MX	
		110040.00	✓	M6C17FC2	26	115/208-230	Man.	5.4	1.15	11.31	S, US	
		110308.00	✓	A6C17FC8	28	115/208-230	Auto.	5.4	1.15	11.31	S, US	
		1200	56C	110414.00	✓	C6K11FC2	42	115/208-230	None	5.3	1.00	13.31
1200	56C	LM24739	C/A	SRF60.75TLCN1B6028	41	115/208-230	None	5.7	1.15	13.82	S, MX, 53	

▼ LM Numbers are Lincoln Models

C/A - Check Availability

Specifications are subject to change without notice

♥ Note listing on inside back flap

Continued On Next Page

