

Single Phase - C Face Motors

Totally Enclosed - Capacitor Start - General Purpose

Single Phase - Totally Enclosed - C Face Less Base

HP	SYN RPM 60 Hz	NEMA Frame	▼ Catalog Number	Stock	Model Number	App. Wgt. (lbs)	Voltage	Over-load Prot.	F. L. Amps @ 230 V	Service Factor	"C" Dim. (Inches)	♥Notes
1	3600	56C	110416.00	✓	C6C34FC10	28	115/208-230	None	6.0	1.15	11.81	S, US
	3600	56C	LM24740	✓	SRF2S1TLCN1C6028	31	115/208-230	None	6.2	1.15	12.32	S, MX
	3600	56C	110415.00	✓	M6C34FC9	28	115/208-230	Man.	6.0	1.15	11.81	S, US
	1800	56C	110058.00	✓	C6C17FC7	33	115/208-230	None	6.4	1.15	11.81	S, US
	1800	56C	LM24614	✓	SRF4S1TLCN1C6028	32	115/208-230	None	6.7	1.15	12.82	S, MX
	1800	56C	110041.00	✓	M6C17FC3	29	115/208-230	Man.	6.4	1.15	11.81	S, US
	1800	143TC	121001.00	✓	C143C17FC2	32	115/208-230	None	6.4	1.15	12.25	S, US
1 1/2	3600	56C	110419.00	✓	C6C34FC12	31	115/208-230	None	8.5	1.00	12.31	S, US
	3600	56C	LM24535	✓	SRF2S1.5TLCN1B6028	35	115/208-230	None	7.1	1.15	12.82	S, MX, 53
	3600	56C	110418.00	✓	M6C34FC11	31	115/208-230	Man.	8.5	1.00	12.31	S, US
	3600	143TC	120101.00	✓	C143C34FC1	36	115/208-230	None	8.5	1.00	12.75	S, US
	1800	56C	110420.00	✓	C6K17FC2	37	115/208-230	None	8.6	1.00	12.81	S, US, 53
	1800	56C	LM24622	✓	SRF4S1.5TLCN1B6028	41	115/208-230	None	7.6	1.15	13.82	S, MX, 53
	1800	56C	110042.00	✓	M6K17FC1	40	115/208-230	Man.	8.6	1.00	12.81	S, US
	1800	145TC	120017.00	✓	C145K17FC3	40	115/208-230	None	8.6	1.00	13.75	S, US, 53
	2	3600	56C	110422.00	✓	C6C34FC14	40	115/208-230	None	10.0	1.00	13.31
3600		56C	LM24530	✓	SRF2S2TLCNB6038	40	115/208-230	None	9.0	1.15	13.32	S, MX, 53
3600		56C	110421.00	✓	P6C34FC13	41	115/208-230	Man.	10.0	1.00	13.31	S, US
3600		145TC	120102.00	✓	C145C34FC2	43	115/208-230	None	10.0	1.00	13.75	S, US
1800		56C	112136.00	✓	C6K17FC9	41	115/230	None	9.2	1.00	13.31	S, US, 53
1800		145TC	120060.00	✓	P145K17FC2	45	115/230	Man.	10.0	1.00	14.25	S, US, 53
1800		182TC	131516.00	C/A	C182C17FC3	64	115/208-230	None	12.4	1.00	14.47	S, MX
3	3600	145TC	120824.00	✓	P145K34FC6	56	230	Man.	13.0	1.00	14.25	S, US, 53
	1800	184TC	131545.00	✓	C184C17FC4	82	115/208-230	None	16.8	1.00	16.47	S, MX
5	3600	184TC	131778.00	✓	C184K34FC2	81	208-230	None	19.8	1.15	16.97	S, MX, 53
	1800	184TC	131540.00	✓	C184K17FC6	104	230	None	23.0	1.00	17.47	S, MX, 53

▼ LM Numbers are Lincoln Models

C/A - Check Availability

Specifications are subject to change without notice

♥ Note listing on inside back flap

Continued On Next Page



Tech Information

Single Phase
ODP Motors

Single Phase
TEFC Motors

Single Phase
C Face Motors

Three Phase
ODP Motors

Three Phase
TEFC Motors

Three Phase
C Face Motors

Inverter Duty
Motors

Severe Duty
Motors