

# Single Phase C Face Motors

## Totally Enclosed - Capacitor Start - General Purpose

### Single Phase - Totally Enclosed - C Face With Base

HP	SYN RPM 60 Hz	NEMA Frame	▼ Catalog Number	Stock	Model Number	App. Wgt. (lbs)	Voltage	Over-load Prot.	F. L. Amps @ 230 V	Service Factor	"C" Dim. (Inches)	♥ Notes	
1/4	1800	S56C	102916.00	✓	C4C17FK4	22	115/208-230	None	2.7	1.15	9.69	S, MX	
		S56C	LM24723	✓	SRF4S0.25TLC6028	17	115/208-230	None	2.1	1.15	10.19	S, MX	
1/3	3600	S56C	102929.00	✓	C4C34FK16	22	115/208-230	None	2.8	1.15	9.69	S, MX	
		S56C	102930.00	✓	C4C17FK6	24	115/208-230	None	3.1	1.15	10.44	S, MX	
	1800	S56C	LM24600	✓	SRF4S0.33TLC1C6028	23	115/208-230	None	3.0	1.15	10.44	S, MX	
		S56C	103082.00	✓	M4C17FK7	24	115/208-230	Man.	3.1	1.15	10.31	S, MX	
1/2	3600	S56C	102903.00	✓	C4C17NK2	25	115/208-230	None	2.6	1.15	10.31	S, MX	
		S56C	102910.00	✓	C4C34FK17	25	115/208-230	None	3.5	1.15	9.94	S, MX	
	3600	S56C	LM24725	✓	SRF2S0.5TLC1C6028	23	115/208-230	None	4.2	1.15	11.82	S, MX	
		S56C	102907.00	✓	C4C17FK5	22	115/208-230	None	4.0	1.15	10.69	S, MX	
	1800	S56C	LM24628	✓	SRF4S0.5TLC6028	24	115/208-230	None	4.0	1.15	11.19	S, MX	
		S56C	103085.00	✓	M4C17FK8	22	115/208-230	Man.	4.0	1.15	10.69	S, MX	
	3/4	3600	S56C	112135.00	✓	C6C34FK36	26	115/208-230	None	5.0	1.15	11.31	S, US
			S56C	LM24726	✓	SRF2S0.75TLC1C6028	30	115/208-230	None	5.3	1.15	12.32	S, MX
1800		S56C	110905.00	✓	C6C17FK4	26	115/208-230	None	5.4	1.15	11.31	S, US	
		S56C	LM24615	✓	SRF2S0.75TLC1C6028	30	115/208-230	None	5.5	1.15	12.32	S, MX	
1	3600	S56C	116922.00	✓	M6C17FK86	26	115/208-230	Man.	5.4	1.15	11.31	S, US	
		S56C	110180.00	✓	C6C34FK1	28	115/208-230	None	6.0	1.15	11.81	S, US	
	3600	S56C	LM24727	✓	SRF2S1TLC1C6028	32	115/208-230	None	6.2	1.15	12.32	S, MX	
		S56C	115877.00	✓	M6C34FK78	28	115/208-230	Man.	6.0	1.15	11.81	S, US	
	1800	S56C	110908.00	✓	C6C17FK5	30	115/208-230	None	6.4	1.15	11.81	S, US	
		S56C	LM24616	✓	SRF4S1TLC6028	35	115/208-230	None	6.7	1.15	12.82	S, MX	
	1800	S56C	115879.00	✓	M6C17FK80	32	115/208-230	Man.	6.4	1.15	11.81	S, US	
		143TC	121680.00	✓	C143C17FK1	32	115/208-230	None	6.4	1.15	12.25	S, US	
	1 1/2	3600	S56C	110909.00	✓	C6C34FK19	34	115/208-230	None	8.5	1.00	12.31	S, US
			S56C	LM24539	✓	SRF2S1.5TLC1B6028	35	115/208-230	None	7.1	1.15	12.82	S, MX
3600		S56C	115024.00	✓	M6K34FK16	35	115/208-230	Man.	6.2	1.15	12.31	S, US	
		S56C	110910.00	✓	C6K17FK2	39	115/208-230	None	8.6	1.00	12.81	S, US	
1800		S56C	LM24728	✓	SRF2S1.5TLC1B6028	41	115/208-230	None	7.6	1.15	13.82	S, MX	
		S56C	116703.00	✓	M6K17FK50	42	115/208-230	Man.	8.6	1.15	12.81	S, US	
1800	145TC	121681.00	✓	C145K17FK13	40	115/208-230	None	8.6	1.00	13.75	S, US		

▼ LM Numbers are Lincoln Models

C/A - Check Availability

Specifications are subject to change without notice

♥ Note listing on inside back flap

Continued On Next Page

