



Three Phase ODP Motors

General Purpose - Standard, EPAct and Premium Efficient Motors

Three Phase - Drip-Proof - Rigid Base

HP	SYN RPM 60 Hz	NEMA Frame	▼ Catalog Number	Stock	Model Number	App. Wgt. (lbs)	Voltage	F. L. Amps @ 230 V	% F.L. Eff.	Service Factor	"C" Dim. (Inches)	Inverter speed range	♥ Notes
1/4	1800	S56	100027.00	✓	C4T17DH1	16	208-230/460	1.4	58.0	1.00	9.20	S, MX	S, MX
	1800	48	LM24866	✓	SPD4S0.25T61	19	230/460	1.3	62.0	1.35	9.30	S, US	S, US
1/3	3600	48	101447.00	✓	C4T34DB3	14	208-230/460	1.4	68.0	1.35	9.00	S, US	S, US
	1800	48	100446.00	✓	C4T17DB2	17	208-230/460	1.6	64.3	1.35	9.10	S, MX	S, MX
	1800	S56	100028.00	✓	C4T17DH2	18	208-230/460	1.6	64.3	1.35	9.50	S, MX	S, MX
	1800	S56	LM24152	✓	SRD4S0.33T61	15	230/460	1.6	67.0	1.35	11.00	S, MX	S, MX
	1800	S56	103017.00	✓	C4T17DH39	23	208-230/460	1.3	77.0	1.25	10.20	S, MX	S, MX
	1200	56	110425.00	✓	C6T11DB3	23	208-230/460	1.6	65.0	1.15	9.90	S, US	S, MX
1/2	3600	S56	101448.00	✓	C4T34DH7	17	208-230/460	1.8	69.0	1.25	9.40	S, US	S, US
	3600	56	LM24869	C/A	SRD2S0.5T61	22	230/460	2.2	66.0	1.25	10.40	S, US	S, MX
	1800	S56	100029.00	✓	C4T17DH3	20	208-230/460	2.0	68.0	1.25	10.00	S, MX	S, US
	1800	56	LM24098	✓	SRD4S0.5T61	17	230/460	2.2	70.0	1.25	10.50	S, MX	S, US
	1800	S56	103018.00	✓	C4T17DH40	26	208-230/460	1.8	77.0	1.25	10.70	S, MX	S, MX
	1200	56	110027.00	✓	C6T11DB1	22	208-230/460	2.8	66.0	1.15	10.40	S, US	S, MX
3/4	3600	S56	101449.00	✓	C4T34DH8	20	208-230/460	2.4	79.0	1.25	9.90	S, US	S, MX
	3600	56	LM24870	✓	SRD2S0.75T61	21	230/460	3.2	74.0	1.25	10.40	S, US	S, US
	1800	S56	100030.00	✓	C4T17DH4	24	208-230/460	2.8	75.0	1.25	10.50	S, MX	S, MX
	1800	S56	LM24099	✓	SRD4S0.75T61	20	230/460	2.8	75.5	1.25	11.00	S, MX	S, US
	1800	56	116738.00	✓	C6T17DB95	30	208-230/460	2.4	81.5	1.25	10.90	S, US	S, US
	1200	56	110028.00	✓	C6T11DB2	17	208-230/460	3.4	75.5	1.15	10.90	S, US	S, MX
1	3600	56	110426.00	✓	C6T34DB1	22	208-230/460	3.2	77.0	1.25	9.80	S, US	S, MX
	3600	56	LM24155	✓	SRD2S1T61	24	230/460	3.7	74.0	1.25	10.40	S, US	S, US
	3600	56	116128.00	✓	C6T34DB30	24	208-230/460	2.8	80.0	1.25	10.20	S, US	S, US
	1800	56	110029.00	✓	C6T17DB1	22	208-230/460	4.2	78.5	1.15	10.40	S, US	S, US
	1800	S56	LM24111	✓	SRD4S1T61	22	230/460	3.4	76.5	1.15	10.50	S, MX	S, US
	1800	56HZ	115827.00	✓	C6T17DB77	24	208-230/460	4.2	78.5	1.15	11.10	S, US, 5	S, US
	1800	56	116752.00	✓	C6T17DB92	36	208-230/460	3.2	85.5	1.25	11.70	S, US	S, US
	1800	143T	121003.00	✓	C143T17DB10	36	208-230/460	3.2	85.5	1.25	12.10	S, US	S, US
	1800	143T	LM24871	✓	SSD4B1T61	35	230/460	3.2	85.5	1.15	12.00	S, MX	S, MX
	1200	145T	121517.00	✓	C145T11DB7	41	208-230/460	3.8	82.5	1.25	12.60	S, US	S, US, 5

Green items are Premium Efficient

▼ LM Numbers are Lincoln Models

C/A - Check Availability

Specifications are subject to change without notice

♥ Note listing on inside back flap

Continued On Next Page

Tech Information

Single Phase ODP Motors

Single Phase TEFC Motors

Single Phase C Face Motors

Three Phase ODP Motors

Three Phase TEFC Motors

Three Phase C Face Motors

Inverter Duty Motors

Severe Duty Motors

