



Product designation

Signal beacons
Ø62mm/2.44"
8LB6EL

Product type designation

General characteristics

Diameter	mm - inch	62 / 2.44
Colour		White
IEC degree of protection		IP54

Mechanical features

Tightening torque for terminals max	Nm	0.5
Terminals screw		Screw clamp terminals
Conductor section		

AWG/Kcmil

max 16

IEC

max mm² 1.5
g 60

Weight


Ambient conditions

Temperature


Operating temperature

min °C -20
max °C +50

Dimensions



Wiring diagrams



Certifications and compliance

Compliance

IEC/EN 60947-1
IEC/EN 60947-5-1

Certificates

EAC

ETIM classification

ETIM 8.0

EC000232 -
Optical module
for signal tower