






Product designation				Enclosed switch disconnecter
Product type designation				GAZ
Number of poles	Nr.			4
Operating voltage type				AC
Contact characteristics				
IEC Conventional free air thermal current I _{th}	A			100
Rated insulation voltage U _i IEC/EN	V			1000
Rated impulse withstand voltage U _{imp}	kV			8
Operating current I _e				
AC21A	400V	A	100	
	500V	A	100	
	690V	A	100	
AC22A	400V	A	100	
	500V	A	100	
	690V	A	100	
AC23A	400V	A	100	
	500V	A	80	
	690V	A	47	
Power dissipation per pole max	W			4
Rated operational power AC23A	400V	kW	55	
	690V	kW	45	
Conditional short-circuit current (rms)	kA			50
Short-circuit protection with fuse	Class/A			gG100
Making capacity AC23A 400V	A			1000
Breaking capacity AC23A 400V	A			800
Mechanical life	cycles			30000
Electrical life AC21A	cycles			30000
Mechanical features				
Operating position	normal allowable			Vertical plan Any
Terminals	type			Pillar
	width	mm	12.4	
	height	mm	10.4	
	screw			M8
	tool			Metric Allen key 4
Tightening torque for terminals	min	Nm	5	
	max	Nm	6	

	min	lbin	45
	max	lbin	54
<hr/>			
Conductor section			
	IEC min	mm ²	4
	IEC max	mm ²	70
	AWG/kcmil min		12
	AWG/kcmil max		1
<hr/>			
UL technical data			
General purpose current rating		A	100
Operating voltage max		V	600
<hr/>			
Horsepower/FLA current single phase motor			
	120V	HP	5/56
	240V	HP	10/50
<hr/>			
Horsepower/FLA current three phase motor			
	240V	HP	30/80
	480V	HP	50/65
	600V	HP	50/52
<hr/>			
Short circuit rating		kA rms	50
Short circuit rating with fuse		Class/A	J/100
<hr/>			
Ambient conditions			
Operating temperature			
	min	°C	-25
	max	°C	+55
<hr/>			
Storage temperature			
	min	°C	-40
	max	°C	+70
<hr/>			
Max altitude		m	3000
<hr/>			
Resistance & Protection			
Frontal IP degree			IP65
UL degree of protection			UL/CSA Type 4/4X
IP degree of protection			IP65
Pollution degree			3
<hr/>			
Dimensions			



Wiring diagrams



Certifications and compliance

Compliance

IEC/EN 60947-1
IEC/EN 60947-3

Certifications

cULus
EAC

ETIM classification

ETIM 8.0

EC000216 -
Switch
disconnecter