



Enclosures with
cut-outs for
Ø22mm units -
with multiholes
for 8 actuators
LPZM

Product designation

Product type designation

General characteristics

Colour	Grey
IEC degree of protection	IP66 and IP67

Mechanical features

Weight	g	1060
--------	---	------

UL technical data

UL degree of protection	NEMA 4X
-------------------------	---------

Ambient conditions

Temperature


Operating temperature

min	°C	-25
max	°C	+70

Storage temperature

min	°C	-40
max	°C	+85

Dimensions



Certifications and compliance

Compliance

IEC/EN 60947-5-1

Certificates

cULus

EAC

ETIM classification

ETIM 8.0

EC000200 -
Enclosure for
control circuit
devices