

# Turbo™ Products

MARS SERIES **121**



## The Turbo® 200 Family Products

Universal Run & Start Capacitor Replacement. Have the right capacitor for the job every time. The perfect solution for off hour emergency service calls.

Universal HardStart Replacement. One “2-Wire” Turbo® Easy-Start “4” Hardstart can replace any one of four compressor hardstart kits on the market.

MARS NO.	DESCRIPTION	MICROFARAD
12100	Turbo® 200 mini	2.5 mfd - 12.5 mfd, 370V or 440V
12200	Turbo® 200	2.5 mfd - 67.5 mfd, 370V or 440V
12300	Turbo® 200 X	5.0 mfd -97.5 mfd, 370V or 440V
11200	Turbolytic™ 50 Universal Motor Start Capacitor	23 mfd -302 mfd, 125V to 330V
11100	Turbolytic™ JR	23 mfd -208 mfd, 125V to 330V
86150	<b>TurboMeter™</b> See the dual values develop simultaneously on the screen as you create the ratings needed.	
12400	Turbo® Easy-Start “4” Hardstart Universal Hardstart	Up to 1 ton 108-130 mfd 1 to 2 tons 189-227 mfd 2.5 to 3 tons 233-280 mfd 3.5 to 5 tons 270 to 324 mfd

## MARS Capacitor Tester

### Features:

- Easy to use
- 9V battery and test leads included
- Low battery indicator

MARS NO.	RANGE	RESOLUTION	ACCURACY	TEST FREQUENCY
65746	200 pF	0, 1pF	± (0.5% rdg + 1 dgt + 0.5 pF)	
	2000 pF 20 nF 200 nF 2 nF	1 pF 10 pF 100 pF 1 nF	± (0.5% rdg +1 dgt)	820Hz
	20 µF	10 nF		82 Hz
	200 µF	100 nF	± (2.0% rdg. + 1dgt)	8.2 Hz
	2000 µF	1 µF		
	20 mF	10 µF	± (4.0% rdg. + 1dgt)	