





# Centrifugal Blowers


MARS SERIES **079**





A064





A079




A080




A090




A118



B24220



A1200



MODEL #	CFM AT STATIC PRESSURE SHOWN STATIC PRESSURE (INCHES OF WATER)					NAME-PLATE		NO. OF SPEEDS	RPM@ FREE AIR	AMPS@ FREE AIR	BRNG	
	0.2	0.4	0.6	0.8	1	CFM	VOLTS					
A064	-	66	65	64	58	64	115	60	1	2400	0.65	SLV
A079	85	81	77	73	65	89	115	60	1	2200	1.1	SLV
A080	78	75	72	68	63	80	115	60	1	2100	1.1	SLV
A090	86	84	78	73	66	90	115	60	1	2300	1.1	SLV
A118	112	110	106	102	97	118	115	60	1	2600	1.8	SLV
B24220	-	140	130	120	110	135	115	50/60	1	2600	1.3	SLV
A1200	1260/1065	1240/1060	1200/1050	1150/1000	1075/950	1200	115/230	60	2	1500/1400	8-6.8/4-3.4	SLV