



Unit Bearing Motors - Shaded Pole

3 1/2 inch dia. MARS SERIES **050**

MARS





51 Frame Unit Bearing Cast Iron Motors

MARS 51 frame motors are used on refrigerators, freezers, food & beverage coolers, vending machines, display cases, and many other fan duty applications.

Features:

- Cast iron construction
- Packed with vibration dampener, speed nut & screws
- Shaded pole, single phase
- Fan duty, continuous, air over
- Impedance protected
- Accessories on pages M-73 to M-75
- Class "B" insulation • 60/50 Hertz



1000 RPM—1/4-20 Threaded Shaft

MARS NO.	WATTS	ROT OSE	VOLTS	AMPS	LEAD LENGTH	A	DIMENSIONS B	C
05111 ⁽¹⁾	2.5	CW	115	0.30	26"	0.66	2.64	1/4

1550 RPM—1/4-20 Threaded Shaft - Dual Pad Mounting - Lyall Plug

MARS NO.	WATTS	ROT OSE	VOLTS	AMPS	LEAD LENGTH	A	DIMENSIONS B	C
05211 ⁽¹⁾	4	CW	115	0.33	24"	0.66	2.64	1/4
05212 ⁽¹⁾	4	CCW	115	0.33	24"	0.66	2.64	1/4
05221 ⁽¹⁾	4	CW	230	0.19	24"	0.66	2.64	1/4
05222 ⁽¹⁾	4	CCW	230	0.19	24"	0.66	2.64	1/4
05311	6	CW	115	0.46	24"	0.66	3.14	1/4
05312	6	CCW	115	0.46	24"	0.66	3.14	1/4
05411	9	CW	115	0.62	24"	0.66	3.14	1/4
05412	9	CCW	115	0.62	24"	0.66	3.14	1/4
05421	9	CW	230	0.33	24"	0.66	3.14	1/4
05422	9	CCW	230	0.33	24"	0.66	3.14	1/4
05811 ⁽²⁾	16	CW	115	0.95	24"	0.66	3.34	1/4
05812 ⁽²⁾	16	CCW	115	0.95	24"	0.66	3.34	1/4
05821 ⁽²⁾	16	CW	230	0.48	24"	0.66	3.34	1/4
05822 ⁽²⁾	16	CCW	230	0.48	24"	0.66	3.34	1/4

1500 RPM—1/4-20 Threaded Shaft

MARS NO.	WATTS	ROT OSE	VOLTS	AMPS	LEAD LENGTH	A	DIMENSIONS B	C
05911 ⁽²⁾	25	CW	115	1.1	22"	0.50	3.50	1/4
05921 ⁽²⁾	25	CW	230	0.60	22"	0.50	3.50	1/4
05711 ⁽²⁾	35	CW	115	1.4	22"	0.50	3.50	1/4
05721 ⁽²⁾	35	CW	230	0.70	22"	0.50	3.50	1/4

1500 RPM—Smooth Shaft

MARS NO.	WATTS	ROT OSE	VOLTS	AMPS	LEAD LENGTH	A	DIMENSIONS B	C
05511 ⁽²⁾	50	CW	115	1.7	22"	1.50	4.50	3/8
05521 ⁽²⁾	50	CW	230	0.85	22"	1.50	4.50	3/8

1550 RPM—1/4-20 Threaded Shaft - Dual Pad Mounting - Lyall Plug

MARS NO.	WATTS	ROT OSE	VOLTS	AMPS	LEAD LENGTH	A	DIMENSIONS B	C
05614	4	CW	115	0.27	26"	0.66	2.64	1/4
05616	6	CW	115	0.40	26"	0.66	3.14	1/4
05619	9	CW	115	0.50	26"	0.66	3.14	1/4
05626	16	CW	115	1.0	24"	0.66	3.34	1/4

(1) Class A Insulation (2) Automatic Reset Overload Protection



The largest selection of motors, components and accessories for the HVAC/R Industry

M-31