

# Low Voltage, DC Permanent Magnet TENV and TEFC

## C-Face with Removable Base



**Applications:** Low voltage permanent magnet DC motors are suitable for installations having batteries or generator supplied low voltage DC.

- Features:**
- Permanently lubricated sealed ball bearings
  - NEMA C-Face with removable base
  - Class H insulation
  - Easy brush access with unique brush holder design
  - Oversized brushes for extra long life
  - High starting torque
  - U.L. Recognized and CSA Certified

HP	RPM	DC VOLTS	FRAME	BRGS.	CAT. NO.	MODEL NO.	LIST PRICE	MULT. SYMB.	F.L. AMPS	APPROX. WGT. LBS.	"C" DIM.	FOOT NOTES
<b>1/4</b>	1750	12	56C	TENV	Z660*	56E17T2001	\$498	D1	21.0	24	10.44	85
<b>1/3</b>	1750	12	56C	TENV	Z662*	56E17T2002	\$548	D1	27.0	24	11.44	85
	1750	24	56C	TENV	Z663*	56E17T2003	\$524	D1	13.5	25	10.94	85
<b>1/2</b>	1750	12	56C	TENV	Z664*	56E17T2004	\$569	D1	39.0	30	12.44	85
	1750	24	56C	TENV	Z665*	56E17T2005	\$544	D1	20.0	29	11.94	d,85
<b>3/4</b>	1750	12	56C	TEFC	Z666*	56E17F2008	\$629	D1	58.0	30	13.81	
	1750	24	56C	TEFC	Z667*	56E17F2009	\$568	D1	29.0	30	12.81	85
<b>1</b>	1750	12	56C	TEFC	Z668*	56E17F2010	\$749	D1	80.0	42	13.81	
	1750	24	56C	TEFC	Z669*	56E17F2011	\$690	D1	39.0	40	13.81	d,85

\* Stock Model

**Footnotes:**

- d To be discontinued after current stock is gone
- 85 Not tach adaptable