

# PRODUCT INFORMATION PACKET

Model No: 145TTVR5301

Catalog No: N652

2 HP Washdown Motor, 3 phase, 0 RPM, 208-230/460 V, TZ Frame, TENV  
General Purpose Motors





**Nameplate Specifications**

Output HP	2 Hp	Output KW	1.5 kW
Voltage	208-230/460 V	Speed	0 rpm
Phase	3	Duty	NONE
Insulation Class	NONE	Design Code	NO DESIGN CODE
Frame	TZ	Enclosure	Totally Enclosed Non Ventilated
Thermal Protection	No	Ambient Temperature	40 °C
UL	Recognized	CSA	Y
CE	N	IP Code	-
Number of Speeds	1		

**Technical Specifications**

Electrical Type	Squirrel Cage Inverter Rated	Starting Method	Line Or Inverter
Rotation	Reversible	Mounting	Rigid Base
Motor Orientation	Horizontal	Drive End Bearing	Ball
Opp Drive End Bearing	Unk	Shaft Type	Special Extension
Overall Length	13.25 in	Shaft Diameter	0.875 in
Assembly/Box Mounting	F1 ONLY		

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:10/11/2021